Brother LC225XLC ink cartridge 1 pc(s) Original High (XL) Yield Cyan



Brand : Brother

Product code: LC225XLC

Product name : LC225XLC

- Prints 1,200 pages in accordance with ISO/IEC 24711.
- High quality genuine Brother cartridge.
- Prevents waste to save you paper, time and money.
- Using this Brother LC225XLC original high yield ink cartridge protects your printer warranty
- The LC225XL range of ink cartridges are available as a more economical value pack, reducing your cost per page even further.

The Brother LC225XLC Cyan High Yield Ink Cartridge – Single Pack. Prints 1,200 pages.



Brother LC225XLC ink cartridge 1 pc(s) Original High (XL) Yield Cyan:

The high yield LC225XLC promises vibrant colours every time you print. With this cyan ink cartridge you can reduce downtime and boost productivity, whilst ensuring you get crisp colours even in the most demanding of environments. As it's a high yield cartridge, the LC225XLC lasts longer than a standard cartridge but offers the same excellent quality results.
Brother LC225XLC. Cartridge capacity: High (XL) Yield, Supply type: Single pack, Colour ink page yield: 1200 pages, Printing colours: Cyan, Quantity per pack: 1 pc(s)

Features	
Print technology	Inkjet printing
Compatibility *	Brother MFC-J4420DW, MFC-J4625DW
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1
Colour ink page yield *	1200 pages
Type *	Original
Cartridge capacity	High (XL) Yield
Printing colours *	Cyan
Brand compatibility *	Brother
Supply type *	Single pack
Country of origin	Philippines
Weight & dimensions	
Width	25 mm
Depth	93 mm
Height	116 mm
Weight	40 g

Packaging data	
Package weight	73 g
Package type	Blister
Other features	
Page yield footnote	ISO / IEC 24711
Paper dimensions	A4
Logistics data	
Pallet gross height	14.8 cm
Products per pallet	3000 pc(s)
Master (outer) cases per pallet	30 pc(s)
Layers per pallet	5 pc(s)
Master (outer) cases per pallet layer	6 pc(s)
Pallet gross weight	189.6 kg
Harmonized System (HS) code	84439990
Pallet type	800 x 1200 mm

4977766736046

4977766735957

5054629492116

5715328103085

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date