

dbramante1928 Monaco - iPhone 14 Pro Max - Pacific Blue

Brand : dbramante1928

Product code: MO67PABL1649

Product name : Monaco - iPhone 14 Pro Max - Pacific Blue

Monaco - iPhone 14 Pro Max - Pacific Blue

dbramante1928 Monaco - iPhone 14 Pro Max - Pacific Blue:

Monaco is an impact protective comfort-grip silicone MagSafe case made from recycled plastic materials. You will love how it feels in your hands, as this case has a super soft grip-friendly finish. With easy-to-press buttons and raised edges to protect camera and screen, Monaco offers complete protection of your phone. The integrated MagSafe magnet ensures effortless wireless charging.

- Made from GRS-certified recycled and recyclable plastic materials
- Non-slip grip and a super soft feel
- Custom fit all-around protection
- 3-layer impact protective yet slim design
- Fully MagSafe compatible
- Made without compromising on quality, functionality, and design

dbramante1928 Monaco - iPhone 14 Pro Max - Pacific Blue. Case type: Cover, Brand compatibility: Apple, Compatibility: iPhone 14 Pro Max, Maximum screen size: 17 cm (6.7"), Surface coloration: Monochromatic, Product colour: Blue



Features		Features	
Maximum screen size *	17 cm (6.7")	Brand compatibility *	Apple
Surface coloration	Monochromatic	Closure type	Not applicable
Compatibility *	iPhone 14 Pro Max	Protection features	Impact resistant, Scratch resistant
Case type *	Cover	Easy to apply	✓
Material *	Recycled plastic	Packaging content	
Product colour *	Blue	Quantity per pack	1 pc(s)
Wireless charging	✓	Sustainability	
		Sustainability certificates	Global Recycled Standard (GRS)



5711428016492

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.