

StarTech.com Lightning Car Charger with Coiled Cable, 1m Coiled Lightning Cable, 12W, White, 2 Port USB Car Charger Adapter for Phones and Tablets, Dual USB In Car iPhone Charger

Brand : StarTech.com

Product code: USBLT2PCARW2

Product name : Lightning Car Charger with Coiled Cable, 1m Coiled Lightning Cable, 12W, White, 2 Port USB Car Charger Adapter for Phones and Tablets, Dual USB In Car iPhone Charger

StarTech.com Lightning Car Charger with Coiled Cable, 1m Coiled Lightning Cable, 12W, White, 2 Port USB Car Charger Adapter for Phones and Tablets, Dual Device In Car iPhone Charger (USBLT2PCARW2)
StarTech.com Lightning Car Charger with Coiled Cable, 1m Coiled Lightning Cable, 12W, White, 2 Port USB Car Charger Adapter for Phones and Tablets, Dual USB In Car iPhone Charger. Charger type: Auto, Power source type: Cigar lighter, Charger compatibility: Smartphone. Input voltage: 12 - 24 V, Maximum output voltage: 5 V. USB 2.0 ports quantity: 1. Cable length: 1 m, Product colour: White



Performance		Packaging data	
Charger compatibility *	Smartphone	Package width	110 mm
Power source type *	Cigar lighter	Package depth	130 mm
USB 2.0 ports quantity	1	Package height	50 mm
Lightning connector	✓	Package weight	7.2 g
Charger type *	Auto	Operational conditions	
Cable shielding	Aluminum mylar foil	Operating temperature (T-T)	0 - 40 °C
Design		Storage temperature (T-T)	-25 - 70 °C
Product colour *	White	Operating relative humidity (H-H)	8 - 90%
Cable length	1 m	Certificates	
Power		Compliance certificates	CE
Input voltage	12 - 24 V	Sustainability	
Input current	3 A	Sustainability compliance	✓
Maximum power	12 W	Logistics data	
Maximum output voltage	5 V	Master (outer) case width	405 mm
Port 1 output current	2.1 A	Master (outer) case length	435 mm
Port 2 output current	2.1 A	Master (outer) case height	355 mm
Output current	4200 mA	Products per master (outer) case	60 pc(s)
Weight & dimensions		Other features	
Width	28 mm	Cable jacket material	Polyvinyl chloride (PVC)
Depth	471 mm	Connector contacts plating	Nickel
Height	36 mm		
Weight	6 g		



0065030883757



065030883757

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.