

Philips S Line 272S1MH/00 computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black

Brand : Philips

Product family: S Line

Product code: 272S1MH/00

Product name : 272S1MH/00

Business Monitor 272S1MH LCD monitor with Windows Hello Webcam

Philips S Line 272S1MH/00 computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black:

The Philips S Line monitor provides features that guarantee comfortable working and daily productivity. 3 sided frameless bezel with crisp FHD gives a clearer and wider view. Pop-up webcam with Windows Hello delivers performance and convenience.

Philips S Line 272S1MH/00. Display diagonal: 68.6 cm (27"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	68.6 cm (27")	Swivelling	✓
Display resolution *	1920 x 1080 pixels	Swivel angle range	-180 - 180°
HD type *	Full HD	Tilt adjustment	✓
Native aspect ratio *	16:9	Tilt angle range	-5 - 25°
Display technology *	LED	On Screen Display (OSD)	✓
Panel type *	IPS	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Backlight type	W-LED		
Touchscreen *	✗		
Display brightness (typical)	300 cd/m²	Number of OSD languages	21
Response time *	4 ms	Plug and Play	✓
Anti-glare screen	✓	LED indicators	Operation, Stand-by
Screen shape *	Flat	Power	
Aspect ratio	16:9	Energy efficiency class (SDR) *	E
Contrast ratio (typical) *	1000:1	Energy consumption (SDR) per 1000 hours *	21 kWh
Contrast ratio (dynamic)	50000000:1	Power consumption (typical) *	16.23 W
Dynamic contrast ratio marketing name	SmartContrast	Power consumption (standby) *	0.3 W
Maximum refresh rate *	75 Hz	Power consumption (off)	0.3 W
Viewing angle, horizontal	178°	Power consumption (PowerSave)	11.6 W
Viewing angle, vertical	178°	AC input voltage	100 - 240 V
Display number of colours *	16.7 million colours	AC input frequency	50 - 60 Hz
Pixel pitch	0.3114 x 0.3114 mm	Power supply type	Internal
Pixel density	82 ppi	Operational conditions	
Horizontal scan range	30 - 85 kHz	Operating temperature (T-T)	0 - 40 °C
Vertical scan range	48 - 75 Hz	Storage temperature (T-T)	-20 - 60 °C
Viewable size, horizontal	59.8 cm	Operating relative humidity (H-H)	20 - 80%
Viewable size, vertical	33.6 cm		
Display diagonal (metric)	68.6 cm		
DDC/CI	✓		

Display		Operational conditions	
Haze rate	25%	Operating altitude	0 - 3658 m
Surface hardness	3H	Non-operating altitude	0 - 12192 m
sRGB coverage (typical)	102%	Weight & dimensions	
NTSC coverage (typical)	81%	Width (with stand)	613 mm
Display sRGB	✓	Depth (with stand)	205 mm
Performance		Height (with stand)	537 mm
NVIDIA G-SYNC *	✗	Weight (with stand)	6.22 kg
AMD FreeSync *	✗	Width (without stand)	613 mm
Fast charging	✓	Depth (without stand)	51 mm
VESA Adaptive Sync support	✓	Height (without stand)	366 mm
Component video sync	Separate Sync, Sync-on-green (SOG)	Weight (without stand)	4.35 kg
Flicker-free technology	✓	Packaging data	
Low Blue Light technology	✓	Package width	700 mm
Multimedia		Package depth	215 mm
Number of speakers	2	Package height	456 mm
RMS rated power	2 W	Package weight	9.62 kg
Built-in speaker(s) *	✓	Packaging content	
Megapixel (approx.)	2 MP	Stand included	✓
Built-in microphone	✓	Cables included	VGA, HDMI, DisplayPort, USB Type-A to USB Type-B, Audio (3.5mm), AC
Built-in camera *	✓	Quick start guide	✓
Design		Manual	✓
Market positioning *	Home	Bundled software	SmartControl
Product colour *	Black	Sustainability	
Front bezel colour	Black	Sustainability certificates	ENERGY STAR, TCO
Feet colour	Black	Doesn't contain	PVC/BFR, Mercury
Ports & interfaces		Other features	
Built-in USB hub *	✓	Compatible operating systems	Mac OS X, Windows 10 / 8.1 / 8 / 7
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Exterior finish type	Textured
USB upstream port type	USB Type-B	Picture enhancement	SmartImage
USB Type-A downstream ports quantity	3	Regulatory Approvals	CB; FCC Class B; ICES-003; CE Mark; TUV/GS; TUV Ergo; CU-EAC; EAEU RoHS; TUV Eye Comfort certified
VGA (D-Sub) ports quantity	1	Heavy metals free	Hg (mercury)
DVI-D ports quantity	1	EasyRead mode	✓
HDMI *	✓	LowBlue mode	✓
HDMI ports quantity	1	Energy efficiency class (old)	E
HDMI version	1.4	Weight	4.35 kg
DisplayPorts quantity	1	Height	366 mm
DisplayPort version	1.2	Width	613 mm
Audio output	✓	Depth	51 mm
PC Audio in	✓	Compliance certificates	RoHS
HDCP	✓	Mean time between failures (MTBF)	70000 h
HDCP version	1.4	Certification	CB, FCC Class B, ICES-003, CE Mark, TUV/GS, TUV Ergo, SEMKO, CU-EAC, EAEU RoHS, TUV Eye Comfort certified
Ergonomics		Recycling data	
VESA mounting *	✓	Recyclable packaging material	100%
Panel mounting interface	100 x 100 mm	Post-consumer recycled plastic	85%
Cable lock slot *	✓	Logistics data	
Cable lock slot type	Kensington	Harmonized System (HS) code	85285210
Height adjustment *	✓		
Adjustable height (max)	13 cm		
Pivot	✓		
Pivot angle	-90 - 90°		



8712581794989

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.