APC NetShelter SX, Server Rack Enclosure, 18U, Black, 925H x 600W x 900D mm





Brand : APC

Product code: AR3006

Product name : NetShelter SX, Server Rack Enclosure, 18U, Black, 925H x 600W x 900D mm

NetShelter SX, Server Rack Enclosure, 18U, Black, 925H x 600W x 900D mm

APC NetShelter SX, Server Rack Enclosure, 18U, Black, 925H x 600W x 900D mm:

An industry standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices. APC NetShelter SX, Server Rack Enclosure, 18U, Black, 925H x 600W x 900D mm. Type: Freestanding rack, Rack capacity: 18U, Maximum weight capacity: 409 kg, Key lock, International Protection (IP) code: IP20. Weight: 67.1 kg. Product colour: Black

Features	
Rack capacity *	18U
Type *	Freestanding rack
Maximum weight capacity *	409 kg
Product colour	Black
Side panels included	✔
Key lock	✔
Front door key lock	✔
International Protection (IP) code	IP20
Certification	UL 2416, UL 60950-1, REACH

Weight & dimensions	
Size (imperial)	48.3 cm (19")
Width	600 mm
Depth	900 mm

Weight & dimensions	
Height	925 mm
Weight	67.1 kg
Mounting depth (min)	19.1 cm
Mounting depth (max)	75.6 cm

Packaging data	
Package width	750 mm
Package depth	995 mm
Package height	1060 mm
Package weight	86 kg

Technical details	
Total carbon footprint (kg of CO2e)	260.95
Compliance certificates	RoHS

Logistics data	
Harmonized System (HS) code	85381000



0731304347651



731304347651

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date