Lenovo ThinkStation Quad AIC M.2 SSD interface cards/adapter Internal PCIe



Brand : Lenovo

Product code: 4XH0V09766

Product name : ThinkStation Quad AIC M.2 SSD

- Supports up to four PCIe X4 M.2 SSDs with the following card types 2242, 2260, 2280 and 22110
- Compatible with specific ThinkStation PCs
- Easy to install

ThinkStation Quad AIC M.2 SSD Adapter,

Lenovo ThinkStation Quad AIC M.2 SSD interface cards/adapter Internal PCIe:

The ThinkStation Quad AIC M.2 SSD Adapter will let you add 4 high speed PCIe M.2 SSDs to your PC with an available x4 express expansion slot. It provides you a convenient way to improve your performance and expand overall internal storage.
Lenovo ThinkStation Quad AIC M.2 SSD. Host interface: PCIe, Output interface: PCIe. Product colour: Black, Certification: CE/FCC/RCM/VCCI/BSMI/KCC. Data transfer rate (max): 32 Gbit/s. Windows operating systems supported: Windows 10. Width: 339 mm, Height: 111.2 mm, Weight: 500 g

Ports & interfaces	
Host interface *	PCIe
Output interface *	PCIe
Design	
Internal *	✔
Product colour	Black
Easy to install	✔
Certification	CE/FCC/RCM/VCCI/BSMI/KCC
Features	
Data transfer rate (max)	32 Gbit/s
System requirements	
Windows operating systems supported	Windows 10

Weight & dimensions	
Width	339 mm
Height	111.2 mm
Weight	500 g
Packaging data	
Package width	482 mm
Package depth	171 mm
Package height	62 mm
Package weight	700 g
Package type	Box
Logistics data	
Harmonized System (HS) code	84733020



0193386704027



193386704027

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date