

ASUS ProArt PA328QV computer monitor 80 cm (31.5") 2560 x 1440 pixels Quad HD LED Black

Brand : ASUS

Product family: ProArt

Product code: 90LM00X0-B02370

Product name : PA328QV

- 31.5-inch WQHD (2560 x 1440) HDR display with IPS 178° wide viewing angle panel
 - International color standard 100% sRGB and 100% Rec. 709 wide color gamut
 - Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
 - Extensive connectivity for maximum flexibility, including DisplayPort, HDMI and earphone jack, plus USB hub
 - 75Hz refresh rate and Adaptive-Sync technology (48~75Hz) to animated content with fast action and eliminate screen tearing
 - Ergonomic stand with tilt, swivel, pivot and height adjustments for a comfortable viewing experience, plus VESA wall-mountable
- ProArt Display PA328QV Professional Monitor – 31.5-inch, IPS, WQHD (2560 x 1440), 100% sRGB, 100% Rec.709, Color Accuracy $\Delta E < 2$, Calman Verified, Ergonomic Stand



Display		Ports & interfaces	
Display diagonal *	80 cm (31.5")	DisplayPort version	1.2
Display resolution *	2560 x 1440 pixels	Headphone out *	✓
HD type *	Quad HD	HDCP	✓
Native aspect ratio *	16:9	Ergonomics	
Display technology *	LED	VESA mounting *	✓
Panel type *	IPS	Panel mounting interface	100 x 100 mm
Backlight type	LED	Cable lock slot *	✓
Touchscreen *	✗	Cable lock slot type	Kensington
Display brightness (typical)	350 cd/m ²	Height adjustment *	✓
Response time *	5 ms	Adjustable height (max)	13 cm
Anti-glare screen	✓	Pivot	✓
Screen shape *	Flat	Pivot angle	-90 - 90°
Contrast ratio (typical) *	1000:1	Swivelling	✓
Maximum refresh rate *	75 Hz	Swivel angle range	-30 - 30°
Viewing angle, horizontal	178°	Tilt adjustment	✓
Viewing angle, vertical	178°	Tilt angle range	-5 - 23°
Display number of colours *	1.073 billion colours	Power	
Pixel pitch	0.272 x 0.272 mm	Energy efficiency class (SDR) *	F
Viewable size, horizontal	69.8 cm	Energy efficiency class (HDR) *	G
Viewable size, vertical	39.3 cm	Energy consumption (SDR) per 1000 hours *	32 kWh
Digital horizontal frequency	27 - 112 kHz	Energy consumption (HDR) per 1000 hours *	39 kWh
Digital vertical frequency	24 - 75 Hz	Power consumption (typical) *	26.5 W
High Dynamic Range (HDR) supported	✓	Power consumption (off)	0 W
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)	Power consumption (PowerSave)	0.5 W
Colour gamut standard	sRGB	AC input voltage	100 - 240 V
Colour gamut	100%		
sRGB coverage (typical)	100%		

Performance		Power	
NVIDIA G-SYNC *	✗	AC input frequency	50 - 60 Hz
AMD FreeSync *	✗	Energy efficiency scale	A to G
Flicker-free technology	✓	Weight & dimensions	
Low Blue Light technology	✓	Width (with stand)	714.8 mm
Multimedia		Depth (with stand)	245 mm
Number of speakers	2	Height (with stand)	595.6 mm
RMS rated power	4 W	Weight (with stand)	11.5 kg
Built-in speaker(s) *	✓	Width (without stand)	714.8 mm
Built-in camera *	✗	Depth (without stand)	67.3 mm
Design		Height (without stand)	422.2 mm
Product colour *	Black	Weight (without stand)	7 kg
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Stand included	✓
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Cables included	AC, DisplayPort, HDMI
USB Type-A downstream ports quantity	4	Quick start guide	✓
HDMI *	✓	Other features	
HDMI ports quantity	2	Certification	TCO Certified TÜV Flicker-free TÜV Low Blue Light Calman Verified
HDMI version	2.0	Logistics data	
DisplayPorts quantity	1	Harmonized System (HS) code	85285210



4711081524847



0195553524858



195553524858



5715328234031

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.