

Targus AMB582GL mouse Right-hand RF Wireless + Bluetooth Optical 2400 DPI

Brand : Targus

Product code: AMB582GL

Product name : AMB582GL

Midsized, 2.4 GHz, Bluetooth 5.0, Optical, 2400 DPI, AA battery, Black

Targus AMB582GL mouse Right-hand RF Wireless + Bluetooth Optical 2400 DPI:

Put productivity at your fingertips with the Midsized Comfort Multi-Device Antimicrobial Wireless Mouse. Experience freedom from cords with two wireless connectivity options, 2.4Ghz or Bluetooth®, and the option to easily connect up to three devices. Its adjustable DPI optical sensor (800, 1200, 1600, or 2400) accommodates your desired mouse sensitivity level, so you can work precisely wherever you go.

For an added benefit, this mouse features Targus DefenseGuard™ Antimicrobial Protection*, which creates a cleaner surface and works continuously to protect the mouse by preventing the growth of microorganisms. Unlike topically applied sprays, DefenseGuard™ mice are treated with an antimicrobial additive that does not wear off and lasts for the life of the product.



Mouse		Design	
Number of scroll wheels	1	Surface coloration	Monochromatic
Scrolling directions	Vertical	Power	
Device interface *	RF Wireless + Bluetooth	Power source *	Batteries
Movement detection technology *	Optical	Number of batteries supported	1
Movement resolution *	2400 DPI	Battery type	AA
Buttons type	Pressed buttons	Weight & dimensions	
Scroll type *	Wheel	Width	63.5 mm
Customizable movement resolution	✔	Depth	105 mm
Frequency band	2.4 GHz	Height	38.6 mm
Bluetooth version	5.0	Weight	59 g
Design		Packaging data	
Form factor *	Right-hand	Quantity per pack *	1 pc(s)
Product colour *	Black	Logistics data	
		Harmonized System (HS) code	84716070



0092636353063



092636353063



5051794034530

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.