

ASUS VA24EQSB computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product code: 90LM056F-B04170

Product name : VA24EQSB

- 23.8-inch Full HD (1920 x 1080) LED backlight display with IPS 178° wide viewing angle panel
 - Up to 75Hz refresh rate with Adaptive-Sync technology to eliminate tracing and ensure crisp and clear video playback
 - Extensive connectivity including HDMI, DisplayPort, D-sub and USB hub
 - Ergonomic design with +35° ~ -5° tilt, ±180° swivel, ±90° pivot and 130mm height adjustments for a comfortable viewing experience
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
 - Supports both Adaptive-Sync with NVIDIA GeForce* graphics cards and FreeSync with AMD Radeon graphics cards *Compatible with NVIDIA GeForce GTX 10 series, GTX 16 series, RTX 20 series and newer graphics cards
- ASUS VA24EQSB Eye Care Monitor – 23.8 inch, Full HD, IPS, Frameless, 75Hz, Adaptive-Sync, Low Blue Light, Flicker Free, Ergonomic Design, Wall Mountable



Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	Headphone out *	✓
Display resolution *	1920 x 1080 pixels	HDCP	✓
HD type *	Full HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LED	Panel mounting interface	100 x 100 mm
Panel type *	IPS	Cable lock slot *	✓
Touchscreen *	✗	Cable lock slot type	Kensington
Display brightness (typical)	300 cd/m²	Height adjustment *	✓
Response time *	5 ms	Adjustable height (max)	13 cm
Anti-glare screen	✓	Pivot	✓
Screen shape *	Flat	Pivot angle	-90 - 90°
Contrast ratio (typical) *	1000:1	Swivelling	✓
Contrast ratio (dynamic)	100000000:1	Swivel angle range	-180 - 180°
Maximum refresh rate *	75 Hz	Tilt adjustment	✓
Viewing angle, horizontal	178°	Tilt angle range	-5 - 35°
Viewing angle, vertical	178°	Power	
Display number of colours *	16.7 million colours	Energy efficiency class (SDR) *	E
Pixel pitch	0.2745 x 0.2745 mm	Energy consumption (SDR) per 1000 hours *	18 kWh
Digital horizontal frequency	24 - 84 kHz	Power consumption (typical) *	13.5 W
Digital vertical frequency	48 - 75 Hz	Power consumption (off)	0.3 W
Performance		Power consumption (PowerSave)	0.5 W
NVIDIA G-SYNC *	✗	AC input voltage	100 - 240 V
AMD FreeSync *	✗	Energy efficiency scale	A to G
Flicker-free technology	✓	Weight & dimensions	
Game mode	✓	Width (with stand)	540.4 mm
Multimedia		Depth (with stand)	211.4 mm
Number of speakers	2		

Multimedia		Weight & dimensions	
RMS rated power	4 W	Height (with stand)	450.8 mm
Built-in speaker(s) *	✓	Weight (with stand)	5.2 kg
Built-in camera *	✗	Width (without stand)	540.4 mm
Design		Depth (without stand)	44.4 mm
Product colour *	Black	Height (without stand)	325 mm
		Weight (without stand)	3.2 kg
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Stand included	✓
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Cables included	AC, HDMI, USB Type-A
USB Type-A downstream ports quantity	2	Quick start guide	✓
VGA (D-Sub) ports quantity	1	Other features	
HDMI *	✓	Certification	TCO Certified TÜV Flicker-free TÜV Low Blue Light
HDMI ports quantity	1	Logistics data	
HDMI version	1.4	Harmonized System (HS) code	85285210
DisplayPorts quantity	1		
DisplayPort version	1.2		
Audio input	✓		



4711081557265

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.