

Brother TN-242CMY toner cartridge 1 pc(s) Original Cyan, Magenta, Yellow

Brand : Brother

Product code: TN-242CMY

Product name : TN-242CMY

TN-242CMY, 1.400, ISO/IEC 19798

Brother TN-242CMY toner cartridge 1 pc(s) Original Cyan, Magenta, Yellow:

Das Original Brother TN-242CMY Value Pack enthält die Farben Cyan, Magenta und Gelb und ist perfekt auf die Brother Drucker abgestimmt, dass beste Ergebnisse in brillanten Farben erzielt werden. Die Kartuschen sind leicht zu installieren. Profitieren Sie von langlebigen und hochwertigen Ausdrucken.

Brother berücksichtigt die Auswirkungen auf die Umwelt in jeder Phase des Lebenszyklus Ihrer Tonerkartusche und reduziert den Abfall bei der Entsorgung. Unsere gesamte Hardware und alle unsere Tonerkartuschen sind so gebaut, dass sie die Umwelt so wenig wie möglich belasten. Brother TN-242CMY. Colour toner page yield: 1400 pages, Printing colours: Cyan, Magenta, Yellow, Quantity per pack: 1 pc(s)



Features		Weight & dimensions	
Compatibility *	DCP-9017CDW, DCP-9022CDW, HL-3142CW, HL-3152CDW	Height	389 mm
Quantity per pack *	1 pc(s)	Weight	1.93 kg
Colour toner cartridges quantity	1	Packaging data	
Colour toner page yield *	1400 pages	Package weight	2.6 kg
Type *	Original	Package type	Box
Printing colours *	Cyan, Magenta, Yellow	Other features	
Brand compatibility *	Brother	Certification	ISO/IEC 19798
Supply type *	Single pack	Logistics data	
Built-in drum unit	✓	Master (outer) cases per pallet layer	6 pc(s)
Quantity per box	1 pc(s)	Master (outer) cases per pallet	54 pc(s)
Product colour	Black	Layers per pallet	9 pc(s)
Country of origin	China	Products per pallet	108 pc(s)
Weight & dimensions		Pallet gross height	17.2 cm
Width	223 mm	Pallet gross weight	228.5 kg
Depth	155 mm	Pallet type	1200 x 1000 mm



4977766812856

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.