



APC SRV3KI uninterruptible power supply (UPS) Double-conversion (Online) 3 kVA 2400 W 6 AC outlet(s)

Brand : APC

Product code: SRV3KI

Product name : SRV3KI

SRV 2000VA, 230 Vac, 40 - 70 Hz, 2000 VA / 1600 W, 220 Vac, 240 Vac, 88% max, 48 V
APC SRV3KI. UPS topology: Double-conversion (Online), Output power capacity: 3 kVA, Output power: 2400 W. AC outlet types: C13 coupler, Power plug: C19 coupler, AC outlets quantity: 6 AC outlet(s).
Battery capacity: 9 Ah, Battery capacity: 48 VAh, Battery voltage: 12 V. Form factor: Mini Tower, Product colour: Black, Display type: LCD. Cables included: Input power cable, Output power cable, RS-232, USB cable



Features		Battery	
UPS topology *	Double-conversion (Online)	Number of batteries supported	1
Output power capacity *	3 kVA	Battery recharge time	4 h
Output power *	2400 W	Design	
Input operation voltage (min) *	110 V	Form factor *	Mini Tower
Input operation voltage (max) *	285 V	Product colour *	Black
Input frequency *	40 - 70 Hz	Display type	LCD
Output operation voltage (min)	220 V	Operational conditions	
Output operation voltage (max)	240 V	Operating temperature (T-T)	0 - 40 °C
Surge energy rating	600 J	Storage temperature (T-T)	-20 - 50 °C
Efficiency	88%	Operating relative humidity (H-H)	0 - 95%
Crest factor	3:1	Storage relative humidity (H-H)	0 - 95%
Emergency Power Off (EPO)	✗	Operating altitude	0 - 3000 m
Socket circuit breaker	✓	Non-operating altitude	0 - 15000 m
Ports & interfaces		Packaging content	
AC outlet types	C13 coupler	Cables included	Input power cable, Output power cable, RS-232, USB cable
Power plug	C19 coupler	Manual	✓
AC outlets quantity	6 AC outlet(s)	Weight & dimensions	
USB port	✓	Width	190 mm
USB 2.0 ports quantity	1	Depth	425 mm
Serial interface	✓	Height	336 mm
Serial interface type	RS-232	Weight	26.8 kg
RS-232 ports	1		

Battery		Packaging data	
Battery capacity	9 Ah	Warranty card	✓
Battery capacity	48 VAh	Software CD	✓
Battery voltage	12 V	Package width	325 mm
		Package depth	565 mm
		Package height	465 mm
		Package weight	29 kg
Logistics data			
		Harmonized System (HS) code	85078000



0731304337973



731304337973

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.