

Epson EcoTank ET-M1170 inkjet printer 1200 x 2400 DPI A4 Wi-Fi

Brand : Epson

Product family: EcoTank

Product code: C11CH44401BY

Product name : ET-M1170

- Reduce your printing costs: Economical ink tank printer with lots of ink included
 - Reliable and durable: One-year or 100,000-page warranty
 - Reduce energy usage: Save up to 95% in power consumption
 - Time saving: Wi-Fi, double-sided printing, 250-sheet tray, mobile printing
 - Fast, business-quality printing: 20ppm print speeds³, no warm up time, PrecisionCore printhead
- A4, Monochrome, Inkjet, Duplex printing, 1200 x 2400DPI, GDI, USB, Ethernet, Wi-Fi
 Epson EcoTank ET-M1170. Maximum duty cycle: 20000 pages per month. Maximum resolution: 1200 x 2400 DPI. Maximum ISO A-series paper size: A4. Print speed (black, normal quality, A4/US Letter): 39 ppm. Duplex printing. Wi-Fi. Product colour: Black, White



Features		Ports & interfaces	
Duplex printing *	✓	USB port *	✓
Page description languages *	GDI	Standard interfaces	Ethernet, USB, Wireless LAN
Colour *	✗	Network	
Maximum duty cycle *	20000 pages per month	Ethernet LAN *	✓
Printing		Wi-Fi *	✓
Maximum resolution *	1200 x 2400 DPI	Wi-Fi Direct *	✓
Print speed (black, normal quality, A4/US Letter) *	39 ppm	Security algorithms	64-bit WEP, 128-bit WEP, WPA-PSK, WPA-TKIP, WPA2-AES, WPA2-PSK
Time to first page (black, normal)	6 s	Mobile printing technologies	Epson Connect, Epson Email Print, Epson Remote Print, Epson iPrint, Google Cloud Print
Duplex print speed (black, normal quality, A4/US Letter)	9 ppm	Design	
Input & output capacity		Market positioning *	Home & office
Total number of input trays *	1	Product colour *	Black, White
Total input capacity *	250 sheets	Power	
Total output capacity *	100 sheets	Power consumption (printing) *	13 W
Paper input type	Paper tray	Power consumption (off)	0.2 W
Paper handling		Power consumption (ready)	3.3 W
Maximum ISO A-series paper size *	A4	AC input voltage	100 - 240 V
Paper tray media types *	Envelopes, Plain paper	System requirements	
Multi-purpose tray media types	Envelopes, Plain paper	Windows operating systems supported	✓
ISO A-series sizes (A0...A9) *	A4, A5, A6	Mac operating systems supported	✓
ISO B-series sizes (B0...B9)	B5, B6	Server operating systems supported	Windows Server 2008, Windows Server 2008 R2, Windows Server 2008 x64, Windows Server 2012 R2, Windows Server 2012 x64, Windows Server 2016
Non-ISO print media sizes	Legal	Weight & dimensions	
Envelopes sizes	10, C6, DL	Width	375 mm
Paper tray media weight	64 - 256 g/m ²	Depth	347 mm
		Height	151 mm
		Weight	4.3 kg
		Logistics data	
		Harmonized System (HS) code	84433210



8715946663555

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.