



Lenovo 4X81E21569 stylus pen 3.6 g Black

Brand : Lenovo
Product code: 4X81E21569
Product name : 4X81E21569

- Diameter: 5.3mm, length:119.9mm
 - Up to 4096 levels of pressure sensitivity
 - Rapid charge 15s for more than 30mins continuous use, and 5 minutes for max 1hour use
 - Integrated storage and charging in notebook
 - Protocol AES 1.0
 - Enter sleep mode when pressure level is 0 and side switch is not pressed within 10mins
- ThinkPad Pen Pro-11 for X13 Yoga Gen 2

Lenovo 4X81E21569 stylus pen 3.6 g Black:

ThinkPad Pen Pro-11 with up to 4096 levels of pressure sensitivity, provides a natural pencil-like and paper experience when you sketch and jot down notes. Users will also enjoy easy access to short-cut functions through two built-in customizable buttons on the base of the pen. This pen can also be conveniently stored and charged in the notebook’s pen slot.
Lenovo 4X81E21569. Device compatibility: Laptop, Brand compatibility: Lenovo, Product colour: Black. Weight: 3.6 g, Width: 119.9 mm, Tip diameter: 5.3 mm. Quantity per pack: 1 pc(s), Package type: Box, Package width: 43 mm

Features		Packaging data	
Device compatibility *	Laptop	Quantity per pack	1 pc(s)
Brand compatibility *	Lenovo	Package type	Box
Compatibility	X13 Yoga Gen 2	Package width	43 mm
Product colour *	Black	Package depth	73 mm
Ergonomic grip	✓	Package height	219 mm
Certification	CE COC ROHS IC VOC NCC FCC EAC ICES	Package weight	80 g
Weight & dimensions		Operational conditions	
Weight	3.6 g	Operating temperature (T-T)	5 - 40 °C
Width	119.9 mm	Operating relative humidity (H-H)	30 - 80%
Tip diameter	5.3 mm		



0195892027874



195892027874

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.