

ASUS BE279QSK computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LCD Black

Brand : ASUS

Product code: 90LM04P1-B03370

Product name : BE279QSK

- Integrated Full HD webcam, mic array and stereo speakers for video conferencing and online learning
 - 27-inch Full HD(1920x1080) frameless IPS panel with wide viewing angles
 - Extensive connectivity with DisplayPort, HDMI, D-sub, Audio in and Earphone jack for the most flexibility
 - Ergonomic design with +35° ~ -5° tilt, ±180° swivel, ±90° pivot and 150mm height adjustments for a comfortable viewing experience
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- BE279QSK Video Conferencing Monitor - 27 inch, Full HD, IPS, Frameless, Full HD Webcam, Mic Array, Stereo Speakers, Height Adjustable, Ergonomic Design, HDMI, Eye Care, Low Blue Light, Flicker Free, Wall Mountable



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	DisplayPort version	1.2
Display resolution *	1920 x 1080 pixels	Headphone out *	✓
HD type *	Full HD	PC Audio in	✓
Native aspect ratio *	16:9	HDCP	✓
Display technology *	LCD	Ergonomics	
Panel type *	IPS	VESA mounting *	✓
Touchscreen *	✗	Panel mounting interface	100 x 100 mm
Display brightness (typical)	250 cd/m²	Cable lock slot *	✓
Response time *	5 ms	Cable lock slot type	Kensington
Anti-glare screen	✓	Height adjustment *	✓
Screen shape *	Flat	Adjustable height (max)	15 cm
Contrast ratio (typical) *	1000:1	Pivot	✓
Contrast ratio (dynamic)	100000000:1	Pivot angle	90 - -90°
Maximum refresh rate *	60 Hz	Swivelling	✓
Viewing angle, horizontal	178°	Swivel angle range	180 - -180°
Viewing angle, vertical	178°	Tilt adjustment	✓
Display number of colours *	16.7 million colours	Tilt angle range	35 - -5°
Pixel pitch	0.311 x 0.311 mm	Power	
Viewable size, horizontal	59.8 cm	Energy efficiency class (SDR) *	C
Viewable size, vertical	33.6 cm	Energy consumption (SDR) per 1000 hours *	14 kWh
Digital horizontal frequency	30 - 83 kHz	Power consumption (typical) *	30 W
Digital vertical frequency	50 - 61 Hz	Power consumption (max)	30 W
Performance		Power consumption (off)	0 W
NVIDIA G-SYNC *	✗	Power consumption (PowerSave)	0.5 W
AMD FreeSync *	✗	Weight & dimensions	
Flicker-free technology	✓		
Low Blue Light technology	✓		
Game mode	✓		

Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	398 mm
RMS rated power	4 W	Depth (with stand)	266 mm
Built-in speaker(s) *	✓	Height (with stand)	548 mm
Megapixel (approx.)	2 MP	Weight (with stand)	6.8 kg
Built-in microphone	✓	Width (without stand)	611 mm
Built-in camera *	✓	Depth (without stand)	56 mm
Design		Height (without stand)	398 mm
Market positioning *	Business	Weight (without stand)	4.8 kg
Product colour *	Black	Packaging data	
Frameless design	✓	Package width	712 mm
Detachable stand	✓	Package depth	228 mm
Feet colour	Black	Package height	468 mm
Ports & interfaces		Package weight	9.3 kg
Built-in USB hub *	✓	Package type	Box
USB upstream port type	USB Type-B	Packaging content	
VGA (D-Sub) ports quantity	1	Stand included	✓
HDMI *	✓	Cables included	AC, DisplayPort, HDMI, USB Type-A to USB Type-B
HDMI ports quantity	1	Quick start guide	✓
HDMI version	1.4	Other features	
DisplayPorts quantity	1	Certification	TÜV Flicker-free TÜV Low Blue Light
		Logistics data	
		Harmonized System (HS) code	85285210



4711081091103

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.