

Epson EcoTank ET-8550 Inkjet A3+ 5760 x 1440 DPI 32 ppm Wi-Fi

Brand : Epson

Product family: EcoTank

Product code: C11CJ21401CE

Product name : ET-8550

EcoTank ET-8550 A3+ Wi-Fi Ink Tank Photo Printer

Epson EcoTank ET-8550 Inkjet A3+ 5760 x 1440 DPI 32 ppm Wi-Fi:

Print up to 2,300 photos with the included ink bottles*. Unleash your creativity with stunning A3+ photos and documents at incredibly low cost-per-page. Print, copy and scan with ease using the impressive 10.9cm colour touchscreen, 5-way media handling and innovative 6-colour ink system. With no messy cartridges to replace and flexible connectivity features this is the perfect printer for the artistic modern family.

Epson EcoTank ET-8550. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 5760 x 1440 DPI, Print speed (colour, normal quality, A4/US Letter): 32 ppm. Scanning: Colour scanning, Optical scanning resolution: 1200 x 4800 DPI. Maximum ISO A-series paper size: A3+. Wi-Fi. Product colour: Black



Printing		Ports & interfaces	
Print technology *	Inkjet	USB port	✓
Printing *	Colour printing	Network	
Duplex printing *	✓	Wi-Fi *	✓
Maximum resolution *	5760 x 1440 DPI	Ethernet LAN *	✓
Print speed (black, normal quality, A4/US Letter) *	32 ppm	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)
Print speed (colour, normal quality, A4/US Letter)	32 ppm	Performance	
Print speed (ISO/IEC 24734) black	16 ppm	Card reader integrated	✓
Print speed (ISO/IEC 24734) colour	12 ppm	Compatible memory cards	SD
Borderless printing	✓	Design	
DVD/CD printing	✓	Product colour *	Black
Copying		Market positioning *	Home & office
Duplex copying *	✗	Built-in display *	✓
Copying *	✗	Display	LCD
Scanning		Control type	Touch
Duplex scanning *	✗	Colour display	✓
Scanning *	Colour scanning	Power	
Optical scanning resolution *	1200 x 4800 DPI	Power consumption (average operating)	17 W
Scan technology	CIS	Power consumption (ready)	7.5 W
Image formats supported	BMP, JPEG, PNG, TIFF	Power consumption (sleep)	0.8 W
Document formats supported	PDF	Power consumption (off)	0.3 W
Fax		Energy Star Typical Electricity Consumption (TEC)	0.16 kWh/week
Faxing *	✗	System requirements	
Features		Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista
Number of print cartridges *	6	Mac operating systems supported	Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks, Mac OS X 11.0 Big Sur
Printing colours *	Black, Cyan, Grey, Magenta, Photo black, Yellow		

Input & output capacity		System requirements	
Total number of input trays *	3	Server operating systems supported Windows Server 2003	
Paper handling		Weight & dimensions	
Maximum ISO A-series paper size *	A3+	Width	523 mm
Paper tray media types *	Envelopes, Photo paper, Plain paper	Depth	379 mm
ISO A-series sizes (A0...A9) *	A3, A3+, A4, A5, A6	Height	169 mm
ISO B-series sizes (B0...B9)	B5, B6	Weight	11.1 kg
Non-ISO print media sizes	Legal, Letter	Packaging data	
Envelopes sizes	10, C6, DL	Package width	660 mm
Photo paper sizes	10x15,13x18 cm	Package depth	459 mm
		Package height	263 mm
		Package weight	14.5 kg
Logistics data			
		Harmonized System (HS) code	84433100



8715946676739

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.