Epson C13T09J24010 ink cartridge 1 pc(s) Original Standard Yield Cyan





Brand : Epson

Product code: C13T09J24010

Product name : C13T09J24010

Singlepack Cyan 408 DURABrite Ultra Ink
Epson C13T09J24010. Colour ink type: Pigment-based ink, Cartridge capacity: Standard Yield, Supply type: Single pack, Colour ink page yield: 1100 pages, Colour ink volume: 14.7 ml, Printing colours: Cyan, Quantity per pack: 1 pc(s)

Features	
Colour ink type	Pigment-based ink
Compatibility *	WorkForce Pro WF-C4810DTWF
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1
Colour ink volume	14.7 ml
Colour ink page yield *	1100 pages
Type *	Original
Cartridge capacity	Standard Yield
Printing colours *	Cyan
Brand compatibility *	Epson
Supply type *	Single pack
Country of origin	China
Packaging data	
Package width	32 mm

Packaging data	
Package depth	98 mm
Package height	142 mm
Package weight	60 g
Sustainability	
Sustainability compliance	✔
Other features	
Compliance certificates	CE
Logistics data	
Products per master (outer) case	8 pc(s)
Master (outer) case gross weight	0 g
Master (outer) case GTIN (EAN/UPC)	8715946704319
Harmonized System (HS) code	84439990
Minimum order quantity	8 pc(s)

8715946701585

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date