Canon i-SENSYS LBP631Cw Colour 1200 x 1200 DPI A4 Wi-Fi

Brand : Canon **Product family:** i-SENSYS **Product code:** 5159C009

Product name : LBP631Cw



- Colour laser office printer for small and medium-sized businesses
- A4 single function printer
- 18 ppm print speed, 5-Line LCD, Wi-Fi, Secure PIN Print
18 ppm, PIN print, Wi-Fi, 5-line LCD, 800MHz x 2, 1200 x 1200 DPI, 30000 pages

Canon i-SENSYS LBP631Cw Colour 1200 x 1200 DPI A4 Wi-Fi:

Canon i-SENSYS LBP631Cw Colour Laser Printer



The Canon i-SENSYS LBP631Cw is a compact laser printer for secure and efficient single-sided colour printing. Save time by printing from your smartphone and boost your business productivity with high quality output at print speeds of up to 18 A4 pages per minute and up to 3,130 A4 pages from high-yield black toner cartridge – or up to 2,350 pages from a set of high-yield colour toner cartridges[1]. The Secure PIN functionality is just one of the robust security features, protecting sensitive documents by preventing automatic printing.

Printing	
Print speed (colour, normal quality, A4/US Letter)	18 ppm
Colour *	✔
Print technology *	Laser
Duplex printing *	✔
Maximum resolution *	1200 x 1200 DPI
Print speed (black, normal quality, A4/US Letter) *	18 ppm
Warm-up time	13 s
Time to first page (black, normal)	10.4 s
Time to first page (colour, normal)	10.5 s

Features	
Maximum duty cycle *	30000 pages per month
Recommended duty cycle	250 - 25000 pages per month
Printing colours *	Black, Cyan, Magenta, Yellow
Page description languages *	UFRII

Input & output capacity	
Total number of input trays *	1
Total input capacity *	250 sheets
Total output capacity *	100 sheets

Paper handling	
Maximum ISO A-series paper size *	A4
Paper tray media types *	Coated paper, Envelopes, Heavy paper, Plain paper, Postcard, Recycled paper
ISO A-series sizes (A0...A9) *	A4, A5
ISO B-series sizes (B0...B9)	B5
Non-ISO print media sizes	Executive, Index card, Legal, Letter

Network	
Ethernet LAN *	✔
Cabling technology	10/100/1000Base-T(X)
Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Security algorithms	64-bit WEP, 128-bit WEP, WPA-AES, WPA-PSK, WPA-TKIP, WPA2-AES, WPA2-PSK, WPA2-TKIP

Performance	
Internal memory *	1000 MB
Built-in processor	✔

Design	
Market positioning *	Business
Product colour *	White
Built-in display *	✔
Display	LCD
Control type	Buttons

Power	
Power consumption (printing) *	390 W
Power consumption (max)	850 W
Power consumption (standby)	8.5 W
Energy Star Typical Electricity Consumption (TEC)	0.19 kWh/week
AC input voltage	220 - 240 V

System requirements	
Windows operating systems supported	Windows 10, Windows 11, Windows 8.1

Paper handling	
Envelopes sizes	C5, Com-10, DL, Monarch
Paper tray media weight	60 - 163 g/m²

Ports & interfaces	
Direct printing *	✔
USB port *	✔
USB 2.0 ports quantity	1

Network	
Wi-Fi *	✔

System requirements	
Mac operating systems supported	Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina, Mac OS X 10.2 Jaguar, Mac OS X 10.3 Panther, Mac OS X 10.4 Tiger, Mac OS X 10.5 Leopard, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks, Mac OS X 11.0 Big Sur, Mac OS X 12.0 Monterey, Mac OS X 13.0 Ventura
Linux operating systems supported	✔
Server operating systems supported	Windows Server 2022

Operational conditions	
Operating temperature (T-T)	10 - 30 °C
Operating relative humidity (H-H)	20 - 80%

Weight & dimensions	
Width	430 mm
Depth	418 mm
Height	287 mm
Weight	14.9 kg

8714574670485

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date