

ASUS TUF Gaming VG27VQM computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product family: TUF Gaming

Product code: 90LM0510-B03E70

Product name : VG27VQM

- 27-inch FHD (1920x1080) 1500R curved gaming monitor with ultrafast 240Hz refresh rate designed for professional gamers and immersive gameplay
 - 1ms (MPRT) response time for smooth gameplay, and ASUS Extreme Low Motion Blur (ELMB™) technology to further reduce ghosting and motion blur
 - FreeSync Premium delivers a seamless, tear-free gaming experience by enabling VRR (variable refresh rate) by default
 - Features an ergonomically designed stand to offer extensive swivel, tilt and height adjustments
 - Supports both Adaptive-Sync with NVIDIA GeForce® graphics cards and FreeSync™ Premium with AMD graphics cards. *Compatible with NVIDIA GeForce GTX 10 series, GTX 16 series, RTX 20 series and newer graphics cards
- TUF Gaming VG27VQM Curved Gaming Monitor – 27 inch Full HD (1920x1080), 240Hz, Extreme Low Motion Blur™, Adaptive-sync, FreeSync™ Premium, 1ms (MPRT)



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	USB hub version	3.2 Gen 1 (3.1 Gen 1)
Display resolution *	1920 x 1080 pixels	USB Type-A downstream ports quantity	2
HD type *	Full HD	HDMI *	✓
Native aspect ratio *	16:9	HDMI ports quantity	2
Display technology *	LED	HDMI version	2.0
Panel type *	VA	DisplayPorts quantity	1
Backlight type	LED	DisplayPort version	1.2
Touchscreen *	✗	Headphone out *	✓
Display brightness (typical)	350 cd/m²	Headphone outputs	1
Response time (MPRT)	1 ms	HDCP	✓
Anti-glare screen	✓	HDCP version	2.2
Screen shape *	Curved	Ergonomics	
Screen curvature rating	1500R	VESA mounting *	✓
Contrast ratio (typical) *	3000:1	Panel mounting interface	100 x 100 mm
Contrast ratio (dynamic)	100000000:1	Cable lock slot *	✓
Dynamic contrast ratio marketing name	ASUS Smart Contrast Ratio (ASCR)	Cable lock slot type	Kensington
Maximum refresh rate *	240 Hz	Height adjustment *	✓
Viewing angle, horizontal	178°	Adjustable height (max)	12 cm
Viewing angle, vertical	178°	Swivelling	✓
Display number of colours *	16.7 million colours	Swivel angle range	90° - -90°
Response time (fast)	1 ms	Tilt adjustment	✓
Pixel pitch	0.311 x 0.311 mm	Tilt angle range	-5° - 25°
Horizontal scan range	30 - 292 kHz	Power	
Vertical scan range	48 - 240 Hz	Energy efficiency class (SDR) *	E
Viewable size, horizontal	29.8 cm	Energy efficiency class (HDR) *	G
Viewable size, vertical	33.6 cm	Energy consumption (SDR) per 1000 hours *	21 kWh
Digital horizontal frequency	292 - 292 kHz		
Digital vertical frequency	48 - 240 Hz		

Display		Power	
Colour gamut standard	sRGB	Energy consumption (HDR) per 1000 hours *	30 kWh
Colour gamut	105%	Energy efficiency scale	A to G
Performance		Weight & dimensions	
AMD FreeSync *	✓	Width (with stand)	609 mm
AMD FreeSync type	FreeSync Premium	Depth (with stand)	211.2 mm
Flicker-free technology	✓	Height (with stand)	386.9 mm
Low Blue Light technology	✓	Weight (with stand)	6 kg
Game mode	✓	Width (without stand)	609 mm
Multimedia		Depth (without stand)	44 mm
Number of speakers	2	Height (without stand)	359.9 mm
RMS rated power	2 W	Weight (without stand)	3.77 kg
Built-in speaker(s) *	✓	Packaging data	
Design		Package width	682 mm
Market positioning *	Gaming	Package depth	448 mm
Product colour *	Black	Package height	209 mm
Ports & interfaces		Package weight	8.2 kg
Built-in USB hub *	✓		



4711081714033



0195553714051



195553714051

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.