

Allied Telesis AT-QSFPLR4 network transceiver module Fiber optic 40000 Mbit/s QSFP+

Brand : Allied Telesis

Product code: 990-004757-00

Product name : AT-QSFPLR4

40G QSFP+ LR4, SMF

Allied Telesis AT-QSFPLR4 network transceiver module Fiber optic 40000 Mbit/s QSFP+:

Allied Telesis QSFP Series pluggable optical modules offer the latest industry standard 40 Gigabit Ethernet connectivity in a flexible, small form factor. These hot-swappable transceiver modules simply plug into any compatible Allied Telesis product.

Allied Telesis AT-QSFPLR4. SFP transceiver type: Fiber optic, Maximum data transfer rate: 40000 Mbit/s, Interface type: QSFP+. Product colour: Silver. Compliance certificates: RoHS, Certification: MSA. Quantity per pack: 1 pc(s)

Performance		Features	
SFP transceiver type *	Fiber optic	Product colour	Silver
Maximum data transfer rate *	40000 Mbit/s	Certificates	
Interface type *	QSFP+	Compliance certificates	RoHS
Single-mode fiber (SMF) supported	✓	Certification	MSA
Fiber optic connector	LC	Operational conditions	
SFP transceiver standard	CWDM, LR4	Operating temperature (T-T)	0 - 70 °C
Maximum transfer distance	10000 m	Storage temperature (T-T)	-20 - 85 °C
Networking standards	IEEE 802.3ba	Packaging content	
		Quantity per pack	1 pc(s)



0767035206172



767035206172

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.