

TP-Link AX3000 Whole Home Mesh WiFi System

Brand : TP-Link

Product code: HX510(1-PACK)

Product name : AX3000 Whole Home Mesh WiFi System

- Dual Band WiFi 6: Speeds up to 3000 Mbps—2402 Mbps on 5 GHz and 574 Mbps on 2.4 GHz
 - Boosted Seamless Coverage: Achieve seamless whole home coverage with a clearer and stronger WiFi signal
 - One Unified Network: Multiple units form a whole-home network that auto-selects the best connection as you move around your home
 - Enhanced Security: WPA3 encryption, Multi-SSID, and Parental Controls provide personalized and safer online experience
 - Wi-Fi CERTIFIED EasyMesh™: Experience strong, stable, and seamless wireless connections based on standard mesh technology
 - Easy Setup: Set up your mesh WiFi in minutes with the powerful Aginet app
 - Remote Management: TAUC cloud management, TR-098, TR-181, TR-111, and TR-143 are supported
- 2.4 GHz (574 Mbps), 5 GHz (2402 Mbps), 802.11a/b/g/n/ac/ax, 3× Gigabit Ports, 120 x 120 x 96.5 mm



Design		Features	
Product type	Mesh router	Firewall security	SPI Firewall
Product colour *	White	Parental control	✓
LED indicators	Yes	Ports & interfaces	
Antenna type *	Internal	Ethernet LAN (RJ-45) ports *	3
Reset button	✓	DC-in jack	✓
Wireless LAN features		Certificates	
Wi-Fi band *	Dual-band (2.4 GHz / 5 GHz)	Certification	CE, FCC, Wi-Fi CERTIFIED 6, Wi-Fi CERTIFIED EasyMesh
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)	Operational conditions	
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax)	Operating temperature (T-T)	0 - 40 °C
WLAN data transfer rate (max) *	3000 Mbit/s	Storage temperature (T-T)	-40 - 60 °C
WLAN data transfer rate (first band)	574 Mbit/s	Operating relative humidity (H-H)	10 - 90%
WLAN data transfer rate (second band)	2402 Mbit/s	Storage relative humidity (H-H)	5 - 90%
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11ax, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n	Weight & dimensions	
Security algorithms	WPA3-Personal, WPA-PSK, WPA2-PSK	Width	120 mm
Point-to-point protocol over Ethernet (PPPoE)	✓	Depth	120 mm
Dynamic IP	✓	Height	96.5 mm
Static IP	✓	Packaging content	
Features		Number of products included	1 pc(s)
Quality of Service (QoS) support	✓	AC adapter included	✓
Port forwarding	✓	Number of units included	1 pc(s)
		Ethernet cable	✓
		Quick installation guide	✓



0840030704574



840030704574



4897098686027



4897098684573

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.