PHILIPS

Philips SPK7507B/00 mouse Office Right-hand RF Wireless Optical 3200 DPI



Brand : Philips

Product code: SPK7507B/00

Product name : SPK7507B/00

- High-definition optical tracking for smooth control
- Comfortable ergonomic mouse design feels great
- Buttons last millions of clicks for durability
- Plug-and-play wireless for convenience

5000 series SPK7507B Wireless mouse

Philips SPK7507B/00 mouse Office Right-hand RF Wireless Optical 3200 DPI:



This mouse is made for speed. With 3200 adjustable DPI capability and optical tracking, it is sure to match your toggling in no time.
Philips SPK7507B/00. Form factor: Right-hand. Movement detection technology: Optical, Device interface: RF Wireless, Movement resolution: 3200 DPI, Buttons type: Pressed buttons, Buttons quantity: 6, Scroll type: Wheel. Power source: Batteries. Product colour: Black

Mouse	
Number of scroll wheels	1
Scrolling directions	Vertical
Purpose *	Office
Connectivity technology *	Wireless
Device interface *	RF Wireless
Movement detection technology *	Optical
Movement resolution *	3200 DPI
Buttons type	Pressed buttons
Scroll type *	Wheel
Buttons quantity *	6
Buttons durability (million clicks)	3
Customizable movement resolution	✔
Number of movement resolution modes	5
Frequency band	2.4 GHz

Design	
Form factor *	Right-hand
Ergonomic design	✔

Design	
Product colour *	Black
Surface coloration	Monochromatic

Ergonomics	
Wireless range	15 m

Power	
Power source *	Batteries

System requirements	
Windows operating systems supported	✔
Mac operating systems supported	✔
Linux operating systems supported	✔

Weight & dimensions	
Width	75 mm
Depth	117 mm
Height	39 mm
Weight	97 g

Packaging data	
Quantity per pack *	1 pc(s)

Technical details	
Driver requirement	✘

8712581778897

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date