



BenQ MW809STH Short throw projector 3600 ANSI lumens DLP XGA (1024x768) White

Brand : BenQ

Product code: 9H.JMF77.1JE

Product name : MW809STH

DLP, 1024x768, HDMI, USB

BenQ MW809STH. Projector brightness: 3600 ANSI lumens, Projection technology: DLP, Projector native resolution: XGA (1024x768). Service life of light source: 15000 h. Serial interface type: RS-232, HDMI connector type: Full-size. Product type: Short throw projector, Market positioning: Short throw, Product colour: White. Power source: AC



Projector		Network	
Projector brightness *	3600 ANSI lumens	Smart TV *	✗
Projection technology *	DLP	Ethernet LAN *	✗
Projector native resolution *	XGA (1024x768)	Wi-Fi *	✗
Matrix size	1.24 cm (0.49")	Storage	
Matrix type	DMD	Card reader integrated *	✗
Light source		Features	
Service life of light source *	15000 h	On Screen Display (OSD)	✓
Ports & interfaces		Design	
HDMI connector type	Full-size	Market positioning *	Short throw
USB 2.0 ports quantity	1	Product type *	Short throw projector
Mini-USB 2.0 ports quantity	1	Product colour *	White
Serial interface type *	RS-232	Placement	Desktop
PC Audio in	✓	Cable lock slot	✓
PC Audio out	✓	Cable lock slot type	Kensington
VGA (D-Sub) ports quantity *	3	Display	
HDMI ports quantity *	1	Built-in display *	✗
DVI port *	✗	Power	
AC (power) in	✓	Power source *	AC



4718755082849

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.