Brother DR-241CL printer drum Original

Brand : Brother

Product code: DR-241CL

Product name : DR-241CL



- Delivers 15,000 pages (at one page per job)
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money

The Brother DR241CL Black, Cyan, Magenta and Yellow Drum Unit. Prints 15,000 pages.

Brother DR-241CL printer drum Original:

Keep your office laser printer performing just as it should and ensure your printouts remain the best-possible quality with this genuine Brother DR241CL Drum Unit. The DR241CL is simple to install, reliable and long-lasting, ensuring that print problems won't slow you down.
Brother DR-241CL. Type: Original, Compatibility: Brother HL-3140/HL-3150/HL-3170, DCP-9020CDW MFC-9140CDN, MFC-9330CDW, MFC-9340CDW, Page yield: 15000 pages. Width: 357 mm, Depth: 207 mm, Height: 380 mm. Package width: 384 mm, Package depth: 360 mm, Package height: 217 mm. Pallet gross height: 14.1 cm, Pallet gross weight: 92.1 kg, Master (outer) cases per pallet: 36 pc(s)



Features	
Print technology	LED printing
Printing colours	Black, Cyan, Magenta, Yellow
Compatibility *	Brother HL-3140/HL-3150/HL-3170, DCP-9020CDW MFC-9140CDN, MFC-9330CDW, MFC-9340CDW
Type *	Original
Page yield *	15000 pages
Cartridge return & recycling	✔
Country of origin	China

Weight & dimensions	
Width	357 mm
Depth	207 mm
Height	380 mm
Weight	1.29 kg

Packaging data	
Package width	384 mm

Packaging data	
Package depth	360 mm
Package height	217 mm
Package weight	1 kg

Technical details	
Pallet type	800 x 1200 mm

Logistics data	
Harmonized System (HS) code	84439990
Pallet gross height	14.1 cm
Pallet gross weight	92.1 kg
Master (outer) cases per pallet	36 pc(s)
Master (outer) cases per pallet layer	6 pc(s)
Layers per pallet	6 pc(s)
Products per pallet	36 pc(s)

4977766718523

0013857003797

013857003797

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date