Epson Production Canvas Matte, 610mm x 12,2m



Brand : Epson

Product code: C13S045295

Product name : Production Canvas Matte, 610mm x 12,2m

Production Canvas Matte, 610mm x 12,2m

Epson Production Canvas Matte, 610mm x 12,2m:

This portrait canvas is made from blended cotton and polyester and is specially designed for fine art and photo reproduction, delivering high colour brilliance and uniform colour areas for maximum quality in both full-colour and mono images. The smooth structure allows a very uniform rendering of skintones in applications from photo art to banners, decorations and window displays. It is compatible with both pigment and dye water-based inks.

- Cotton/polyester blend for fine art and photo applications
- Suits photo art, banners, window - display/decoration and exhibition use
- Easy to handle, flexible and durable for exhibition and repeated installation
- Water resistant with a short drying time
- High colour brilliance and uniform coverage
- Supports dye and pigment water-based inks

Epson Production Canvas Matte, 610mm x 12,2m. Roll length: 12.2 m, Roll width: 61 cm, Size (imperial): 61 cm (24"), Finish type: Matt, Print media weight: 320 g/m²

Features	
Roll length *	12.2 m
Roll width *	61 cm
Size (imperial)	61 cm (24")
Print media weight *	320 g/m²
Finish type *	Matt
Country of origin	Switzerland

Operational conditions	
Operating temperature (T-T)	15 - 30 °C
Storage temperature (T-T)	0 - 40 °C
Operating relative humidity (H-H)	40 - 60%
Storage relative humidity (H-H)	10 - 80%

Packaging data	
Quantity per pack	1 pc(s)
Package width	140 mm
Package depth	665 mm
Package weight	3.17 kg
Package height	140 mm

Logistics data	
Master (outer) case length	665 mm
Master (outer) case width	140 mm
Master (outer) case height	140 mm
Pallet gross length	120 cm
Pallet gross width	80 cm
Pallet gross height	56 cm
Products per master (outer) case	1 pc(s)
Products per pallet layer	18 pc(s)
Products per pallet layer (UK)	22 pc(s)
Products per pallet (UK)	72 pc(s)
Pallet length (UK)	120 cm
Pallet width (UK)	100 cm
Pallet height (UK)	56 cm
Harmonized System (HS) code	48025590

Other features	
Products per pallet	72 pc(s)

8715946491356

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date