Brother TN-8000 toner cartridge 1 pc(s) Original Black

Brand : Brother

Product code: TN-8000

Product name : TN-8000



- Prints 2,200 pages in accordance with ISO/IEC19752
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money

The Brother TN-8000 Black Toner Cartridge. Prints 2,200 pages.

Brother TN-8000 toner cartridge 1 pc(s) Original Black:

As it’s the standard colour of many print jobs, you may find that you need to replenish your black cartridge more often. This genuine Brother TN-8000 High Yield Toner Cartridge is capable of printing up to 2,200 pages, producing brilliant results from the very first to the last page you print.
Brother TN-8000. Black toner page yield: 2200 pages, Printing colours: Black, Quantity per pack: 1 pc(s)

Features	
Compatibility *	FAX-8070P MFC-9030 MFC-9070 MFC-9160 MFC-9180
Quantity per pack *	1 pc(s)
Black toner cartridges quantity	1
Black toner page yield *	2200 pages
Type *	Original
Printing colours *	Black
Brand compatibility *	Brother
Supply type *	Single pack
Cartridge capacity	High (XL) Yield
Product colour	Blue, White
Country of origin	China
Weight & dimensions	
Width	60 mm
Depth	270 mm
Height	70 mm

Weight & dimensions	
Weight	164 g
Packaging data	
Package weight	266 g
Other features	
Colour	✕
Print technology	Laser printing
Logistics data	
Harmonized System (HS) code	84439990
Master (outer) cases per pallet layer	12 pc(s)
Master (outer) cases per pallet	144 pc(s)
Layers per pallet	12 pc(s)
Products per pallet	864 pc(s)
Pallet gross height	17.1 cm
Pallet gross weight	247 kg
Pallet type	800 x 1200 mm

4977766601115

4977766629829

0012502607700

012502607700

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date