APC Rack PDU Extender, Basic, 2U, 32A, 230V, (4) IEC 309-32 power distribution unit (PDU) 4 AC outlet(s) Black



Brand : APC

Product code: AP7586

Product name : Rack PDU Extender, Basic, 2U, 32A, 230V, (4) IEC 309-32

RACK PDU BASIC 2U 32A 230V (4) IEC 309-32

APC Rack PDU Extender, Basic, 2U, 32A, 230V, (4) IEC 309-32 power distribution unit (PDU) 4 AC outlet(s) Black:

The most mounting options in the market.
APC offers a wide variety of Basic Rack Power Distribution Units (PDUs), which allow users to distribute power outlets to rack-mount equipment. Horizontal and vertical units are available as well as a variety of power inputs and outputs to fit most power environments. APC now offers Basic Rack PDUs that mount vertically, without tools in the rear channel of a NetShelter VX.
APC Rack PDU Extender, Basic, 2U, 32A, 230V, (4) IEC 309-32. PDU types: Basic, Rack capacity: 2U, Mounting: Horizontal. AC outlets quantity: 4 AC outlet(s), Input connection type: Hard Wire 3-wire, Output connections: (4) IEC 309 . Cable length: 8.53 m. Nominal input voltage: 230 V, Nominal output voltage: 230 V, Output voltage: 230 V. Width: 437 mm, Depth: 89 mm, Height: 89 mm

Design	
PDU types *	Basic
Rack capacity *	2U
Mounting	Horizontal
Product colour	Black
Ports & interfaces	
AC outlets quantity *	4 AC outlet(s)
I/O ports	Hard Wire 3-wire (4) IEC 309
Input connection type	Hard Wire 3-wire
Output connections	(4) IEC 309
Features	
Cable length	8.53 m
Power	
Nominal input voltage *	230 V
Nominal output voltage	230 V
Output voltage	230 V
Load capacity	7680 VA
Maximum input current per phase	32 A

Power	
Maximum total current draw per phase	32 A
Maximum power	7680 W
Operational conditions	
Operating temperature (T-T)	0 - 45 °C
Storage temperature (T-T)	-25 - 65 °C
Operating relative humidity (H-H)	0 - 45%
Storage relative humidity (H-H)	0 - 95%
Weight & dimensions	
Width	437 mm
Depth	89 mm
Height	89 mm
Weight	4.09 kg
Packaging data	
Package weight	5 kg
Package width	521 mm
Package depth	521 mm
Package height	152 mm



0731304224198



731304224198

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date