



APC Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card, Extended runtime, W/ rail kit, 6-year warranty



Brand : APC

Product code: SRT6KRMXLI-6W

Product name : Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card, Extended runtime, W/ rail kit, 6-year warranty

Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card, Extended runtime, W/ rail kit, 6-year warranty

[APC Smart-UPS On-Line, 6kVA/6kW, Rackmount 4U, 230V, 6x C13+4x C19 IEC outlets, Network Card, Extended runtime, W/ rail kit, 6-year warranty:](#)

This APC Smart-UPS is designed for IT professionals or network administrators to maintain business uptime and continuity. This 6kVA on-line 4U rackmount UPS provides pure sine wave power and extended runtime to support critical electronics during power disruptions. It comes with hard wire 3-wire (1P+N+E) input, 6x IEC 320 C13 and 4x IEC 320 C19 outlets, and 2x IEC jumper cables. The UPS has an embedded Network Management Card for UPS network-based monitoring and management. The UPS comes with PowerChute Network Shutdown that provides graceful shutdown of physical servers, virtual machines, and HCI clusters. The UPS can connect to EcoStruxure IT or third-party centralized management platforms. The UPS has a 6-year warranty and comes with a built-in lead-acid battery.

Features		Design	
UPS topology *	Double-conversion (Online)	Rack capacity	4U
Output power capacity *	6 kVA	Product colour *	Black
Output power *	6000 W	Display type	LCD
Waveform *	Sine	LED indicators	Status
Input operation voltage (min) *	100 V	International Protection (IP) code	IP20
Input operation voltage (max) *	275 V	Operational conditions	
Input frequency *	40 - 70 Hz	Operating temperature (T-T)	0 - 40 °C
Output operation voltage (min)	220 V	Storage temperature (T-T)	-15 - 45 °C
Output operation voltage (max)	240 V	Operating relative humidity (H-H)	0 - 95%
Output frequency regulation	50/60 Hz	Storage relative humidity (H-H)	0 - 95%
Surge energy rating	480 J	Operating altitude	0 - 3000 m
Number of output phases	1	Non-operating altitude	0 - 15000 m
Efficiency	94.4%	Certificates	
Crest factor	3:1	Compliance certificates	RoHS
Emergency Power Off (EPO)	✓	Certification	REACH, CE, CE Mark, EAC, EN/IEC 62040-1, EN/IEC 62040-2, IRAM, RCM, VDE
Noise level	55 dB	Packaging content	
Surge protection	✓	Rack mount kit	✓
Audible alarm(s)	✓	Cables included	USB cable
Auto-restart	✓	Management card included	✓
Ports & interfaces		Quick installation guide	✓
AC outlet types	C13 coupler, C19 coupler	Sustainability	
Power plug	Hardwire	Sustainability certificates	ENERGY STAR
AC outlets quantity	10 AC outlet(s)	Weight & dimensions	
Number of output IEC jumpers	2	Width	432 mm
USB port	✓	Depth	719 mm
Serial interface	✓	Height	174 mm
SmartSlot	✓	Weight	60 kg
SmartConnect port	✗	Packaging data	
Battery		Bracket	✓
Battery technology	Sealed Lead Acid (VRLA)		
Battery capacity	902 VAh		
Typical backup time at full load	2.5 min		

Battery		Packaging data	
Typical backup time at half load	8.7 min	Temperature sensor	✓
Battery life (max)	5 year(s)	Warranty card	✓
Battery recharge time	1.5 h	Software CD	✓
Hot-swap battery	✓	Package width	610 mm
Automatic battery test	✓	Package depth	960 mm
Cold start	✓	Package height	370 mm
Design		Package weight	67 kg
Form factor *	Rackmount	Logistics data	
		Products per pallet	6 pc(s)
		Harmonized System (HS) code	85078000
		Total carbon footprint (kg of CO2e)	13539.46
		Other features	
		Packaging content	Web/SNMP Management Card



8592978053499



3606481339003

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.