# APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 800D mm




**Brand :** APC

**Product code:** ER6282

**Product name :** Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 800D mm

Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 800D mm
APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 800D mm. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1199.75 kg, Key lock, Castor wheels. Weight: 94.4 kg. Product colour: Black



| Features | |
|---|---|
| Rack capacity * | 42U |
| Type * | Freestanding rack |
| Maximum weight capacity * | 1199.75 kg |
| Maximum weight capacity (rolling) | 599.65 kg |
| Product colour | Black |
| Side panels included | ✔ |
| Key lock | ✔ |
| Castor wheels | ✔ |
| Preassembled | ✔ |

| Weight & dimensions | |
|---|---|
| Size (imperial) | 48.3 cm (19") |
| Width | 600 mm |
| Depth | 800 mm |
| Height | 1991 mm |
| Weight | 94.4 kg |

| Packaging data | |
|---|---|
| Package weight | 100 kg |

| Technical details | |
|---|---|
| Total carbon footprint (kg of CO2e) | 303.43 |

0731304427841

731304427841

**Catalog Object Cloud**

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date