

Canon i-SENSYS MF552dw Laser A4 1200 x 1200 DPI 43 ppm Wi-Fi

Brand : Canon

Product family: i-SENSYS

Product code: 5160C024

Product name : MF552dw

- Mono laser office printer
 - A4, print, copy, scan
 - 43 ppm, Wi-Fi, 12.7 cm LCD touch screen
 A4, 43ppm, 1200 x 1200 dpi, Secure PIN print, LCD Colour Touch Screen, USB 2.0, LAN, WLAN, 220-240V
 Canon i-SENSYS MF552dw. Print technology: Laser, Printing: Mono printing, Maximum resolution: 1200 x 1200 DPI. Copying: Mono copying, Maximum copy resolution: 600 x 600 DPI. Scanning: Colour scanning, Optical scanning resolution: 600 x 600 DPI. Duplex functions: Copy, Print, Scan. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: Black, White

Printing		Paper handling	
Print technology *	Laser	Envelopes sizes	C5, Com-10, DL, Monarch
Printing *	Mono printing	Paper tray media weight	60 - 120 g/m ²
Duplex printing *	✓	Multi-Purpose Tray media weight	60 - 199 g/m ²
Maximum resolution *	1200 x 1200 DPI	Ports & interfaces	
Print speed (black, normal quality, A4/US Letter) *	43 ppm	Direct printing *	✓
Warm-up time	14 s	USB port	✓
Time to first page (black, normal)	5.7 s	USB 2.0 ports quantity	1
Secure printing	✓	Network	
Copying		Wi-Fi *	✓
Duplex copying *	✓	Ethernet LAN *	✓
Copying *	Mono copying	Cabling technology	10/100/1000Base-T(X)
Maximum copy resolution *	600 x 600 DPI	Ethernet LAN data rates	10,100,1000 Mbit/s
Maximum number of copies	999 copies	Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Copier resize	25 - 400%	Security algorithms	64-bit WEP, 128-bit WEP, WPA-AES, WPA-PSK, WPA-TKIP, WPA2-AES, WPA2-PSK, WPA2-TKIP
N-in-1 copy function	✓	Performance	
N-in-1 copy function (N=)	2, 4	Internal memory *	1024 MB
ID-card copy function	✓	Built-in processor	✓
Scanning		Processor frequency	800 MHz
Duplex scanning *	✓	Sound pressure level (printing)	54 dB
Scanning *	Colour scanning	Sound pressure level (standby)	24 dB
Optical scanning resolution *	600 x 600 DPI	Design	
Scanner type *	ADF scanner	Product colour *	Black, White
Scan to	Cloud, E-mail	Market positioning *	Business
Image formats supported	JPEG, TIFF	Built-in display *	✓
Document formats supported	PDF	Display	LCD
Input colour depth	24 bit	Control type	Touch
Output colour depth	24 bit	Colour display	✓
Greyscale levels	256	Power	
Scan drivers	ICA, TWAIN, WIA	Power consumption (max)	1430 W
Fax		Power consumption (printing)	590 W
Faxing *	✗	Power consumption (standby)	13.6 W
Features		Power consumption (sleep)	0.9 W
Recommended duty cycle	2000 - 75000 pages per month	Energy Star Typical Electricity Consumption (TEC)	0.41 kWh/week
Maximum duty cycle *	150000 pages per month	AC input voltage	220 - 240 V
Duplex functions *	Copy, Print, Scan	System requirements	
Printing colours *	Black		
Page description languages	PCL 5e, PCL 6, PostScript 3, UFR II		
Printer fonts	PCL, PostScript		

Input & output capacity		System requirements	
Total number of input trays *	1	Windows operating systems supported	Windows 10, Windows 11, Windows 8.1
Total input capacity *	550 sheets		Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina, Mac OS X 10.2 Jaguar, Mac OS X 10.3 Panther, Mac OS X 10.4 Tiger, Mac OS X 10.5 Leopard, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks, Mac OS X 11.0 Big Sur
Total output capacity *	150 sheets	Mac operating systems supported	
Multi-Purpose tray	✓		
Multi-Purpose tray input capacity	100 sheets		
Auto document feeder (ADF)	✓		
Auto document feeder (ADF) input capacity	50 sheets	Linux operating systems supported	
Maximum input capacity	2300 sheets		✓
Paper handling		Server operating systems supported	
Maximum ISO A-series paper size *	A4		Windows Server 2008, Windows Server 2008 R2, Windows Server 2012, Windows Server 2012 R2, Windows Server 2016, Windows Server 2019
Paper tray media types *	Envelopes, Heavy paper, Labels, Plain paper, Postcard, Recycled paper, Thin paper		
ISO A-series sizes (A0...A9) *	A4, A5, A6		
ISO B-series sizes (B0...B9)	B5	Operational conditions	
Non-ISO print media sizes	Executive, Legal, Letter, Oficio, Statement	Operating relative humidity (H-H)	20 - 80%
		Storage temperature (T-T)	10 - 30 °C
Weight & dimensions			
		Width	480 mm
		Depth	464 mm
		Height	452 mm
		Weight	19.8 kg
Logistics data			
		Harmonized System (HS) code	84433100



8714574670379

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.