



TP-Link AX3000 Whole Home Mesh WiFi 6 System, 2-Pack

Brand : TP-Link

Product code: DECO X50(2-PACK)

Product name : AX3000 Whole Home Mesh WiFi 6 System, 2-Pack

- AX3000 Dual Band WiFi - Super-fast WiFi 6 with speeds up to 3.0 Gbps
 - 4 Streams, Less Lag - 2x2/HE160 2402 Mbps + 2x2 574 Mbps
 - Gigabit Wired Speed - 3x Gigabit ports provide sufficient connectivity
 - Boosted Seamless Coverage - Seamless mesh WiFi coverage up to 4,500 ft2 (2-pack)
 - AI-Driven Mesh - Intelligently learns the network environment to provide ideal WiFi unique to your home
 - TP-Link HomeShield - Provides comprehensive network protection, robust parental controls, and real-time IoT protection
 - Setup Made Easier Than Ever - The Deco app walks you through the setup step-by-step
- Wi-Fi 6, AX3000, 2.4/5 GHz, 2x2 MU-MIMO, 3x 1G RJ-45, 12V, 110x110x114 mm, 2-pack



Design		Features	
Product colour *	White	Parental control	✓
Antenna type *	Internal	Parental control features	Custom profiles, Time controls, Weekly/monthly reports
Antennas quantity	2	Firmware upgradeable via MU-MIMO technology	Network ✓
Transmit power	CE: <20 dBm (2.4 GHz) <23 dBm (5 GHz) FCC: <30 dBm (2.4 GHz) <30 dBm (5 GHz)	Ports & interfaces	
Reset button	✓	Ethernet LAN (RJ-45) ports *	3
Wireless LAN features		DC-in jack	✓
Wi-Fi band *	Dual-band (2.4 GHz / 5 GHz)	Power	
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)	AC adapter output voltage	12 V
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax)	AC adapter output current	1.5 A
WLAN data transfer rate (first band)	574 Mbit/s	Certificates	
WLAN data transfer rate (second band)	2402 Mbit/s	Compliance certificates	CE, RoHS
Networking standards	IEEE 802.11n, IEEE 802.11a, IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g	Operational conditions	
Security algorithms	WPA-PSK, WPA2-PSK, WPA3-PSK	Operating temperature (T-T)	0 - 40 °C
Number of guest networks (5 GHz)	1	Storage temperature (T-T)	-40 - 70 °C
Number of guest networks (2.4 GHz)	1	Operating relative humidity (H-H)	10 - 90%
IGMP proxy	✓	Storage relative humidity (H-H)	5 - 90%
IGMP snooping	✓	Weight & dimensions	
Tagged VLAN	✓	Width	110 mm
Dynamic DNS (DDNS)	✓	Depth	110 mm
		Height	114 mm
Features		Packaging content	
Built-in processor	✓	Number of products included	2 pc(s)
		AC adapter included	✓
		Number of units included	2 pc(s)


Features		Packaging content	
Processor cores	2	Ethernet cable	✓
Processor frequency	1 GHz	Packaging data	
Quality of Service (QoS) support	✓	Package width	314 mm
Port forwarding	✓	Package depth	240 mm
Firewall security	SPI	Package height	125 mm
BeamForming	✓	Package weight	1.61 kg
DHCP client	✓	Logistics data	
Universal Plug and Play (UPnP)	✓	Harmonized System (HS) code	85171800



4897098687079



4897098681664



4895252500196



0840030707070



840030707070

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.