

Viewsonic LS700HD data projector Standard throw projector 3500 ANSI lumens DMD 1080p (1920x1080) White

Brand : Viewsonic

Product code: LS700HD

Product name : LS700HD

3,500 ANSI Lumens 1080p Laser Home Projector

Viewsonic LS700HD. Projector brightness: 3500 ANSI lumens, Projection technology: DMD, Projector native resolution: 1080p (1920x1080). Light source type: Laser, Service life of light source: 20000 h. Focus: Manual, Focal length range: 12 - 15.6 mm, Aperture range (F-F): 1.9 - 2.49. Analog signal format system: NTSC, PAL, SECAM, Supported graphics resolutions: 640 x 480 (VGA), 1920 x 1080 (HD 1080), Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232, HDMI connector type: Full-size, HDMI version: 1.4a



Projector		Network	
Screen size compatibility *	1524 - 7620 mm (60 - 300")	Ethernet LAN *	✓
Projection distance	1.5 - 8.79 m	Ethernet LAN (RJ-45) ports	1
Projector brightness *	3500 ANSI lumens	Wi-Fi *	✗
Projection technology *	DMD	Storage	
Projector native resolution *	1080p (1920x1080)	Card reader integrated *	✗
Contrast ratio (typical) *	3000000:1	Features	
Number of colours	1.07 billion colours	Interactive *	✗
Horizontal scan range	15 - 102 kHz	Noise level (economic mode)	30 dB
Vertical scan range	23 - 120 Hz	HDCP	✓
Keystone correction, horizontal	-40 - 40°	On Screen Display (OSD)	✓
Keystone correction, vertical	-40 - 40°	On Screen Display (OSD) languages	Arabic, Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Indonesian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Thai, Turkish, Vietnamese
Light source			
Light source type *	Laser		
Service life of light source *	20000 h	Number of OSD languages	22
Lens system		Noise level *	34 dB
Focus *	Manual	Multimedia	
Focal length range	12 - 15.6 mm	Built-in speaker(s) *	✓
Aperture range (F-F)	1.9 - 2.49	RMS rated power	2 W
Zoom capability	✓	Design	
Zoom ratio	2.0:1	Market positioning *	Presentation
Throw ratio	1.13-1.47	Product type *	Standard throw projector
Offset	100%	Product colour *	White
Video		Placement	Desktop, Ceiling
Analog signal format system *	NTSC, PAL, SECAM		
Full HD *	✓		
Supported graphics resolutions	640 x 480 (VGA), 1920 x 1080 (HD 1080)		

Video		Display	
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p	Built-in display *	✗
Ports & interfaces		Power	
HDMI connector type	Full-size	Power source *	AC
HDMI version	1.4a	Power consumption (typical) *	260 W
USB 2.0 ports quantity	1	Power consumption (standby) *	0.5 W
Serial interface type *	RS-232	AC input voltage	100-240 V
PC Audio in	✓	AC input frequency	50 - 60 Hz
PC Audio out	✓	Weight & dimensions	
VGA (D-Sub) ports quantity *	3	Width	396 mm
HDMI ports quantity *	2	Depth	314 mm
Composite video in *	1	Height	157 mm
DVI port *	✗	Weight *	6.65 kg
AC (power) in	✓	Package width	499 mm
Network		Package depth	402 mm
Smart TV *	✗	Package height	261 mm
		Package weight	8.45 kg
		Packaging content	
		Remote control included *	✓
		Cables included	AC, VGA
		Manual	✓
		Logistics data	
		Harmonized System (HS) code	85286200



0766907981216



766907981216

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.