



APC BV800I uninterruptible power supply (UPS) Line-Interactive
0.8 kVA 450 W

Brand : APC

Product code: BV800I

Product name : BV800I

- Best Value UPS with Battery Backup & Surge Protection for Electronics and Computers
- Includes: User Manual
450 W, 800 VA, 50/60 Hz, 230V, 6x IEC 320 C13, IEC-320 C14
APC BV800I. UPS topology: Line-Interactive, Output power capacity: 0.8 kVA, Output power: 450 W. AC outlet types: C13 coupler. Battery technology: Sealed Lead Acid (VRLA), Battery life (max): 5 year(s). Form factor: Compact, Product colour: Black, Cable length: 1.52 m. Compliance certificates: RoHS, Certification: CE



Features		Battery	
UPS topology *	Line-Interactive	Cold start	✓
Output power capacity *	0.8 kVA	Design	
Output power *	450 W	Form factor *	Compact
Waveform *	Sine	Cable length	1.52 m
Input operation voltage (min) *	170 V	Product colour *	Black
Input operation voltage (max) *	280 V	LED indicators	Status
Input frequency *	50/60 Hz	Operational conditions	
Output operation voltage (min)	230 V	Operating temperature (T-T)	0 - 40 °C
Output operation voltage (max)	230 V	Operating relative humidity (H-H)	0 - 90%
Output frequency	50/60 Hz	Certificates	
Automatic Voltage Regulation (AVR)	✓	Compliance certificates	RoHS
Surge energy rating	156 J	Certification	CE
Noise level	40 dB	Packaging content	
Surge protection	✓	Management card included	✗
Audible alarm(s)	✓	Manual	✓
Audible alarm modes	Low battery alarm, Overload alarm	Weight & dimensions	
Ports & interfaces		Width	160 mm
AC outlet types	C13 coupler	Depth	305 mm
SmartSlot	✗	Height	92 mm
SmartConnect port	✗	Weight	5.3 kg
Battery		Packaging data	
Battery technology	Sealed Lead Acid (VRLA)	Package width	143 mm
Battery life (max)	5 year(s)	Package depth	373 mm
		Package height	237 mm
		Package weight	5.6 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0731304338345



731304338345

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.