

Epson WorkForce Pro WF-C8690D3TWFC Inkjet A3+ 4800 x 1200 DPI 35 ppm Wi-Fi

Brand : Epson

Product family: WorkForce Pro **Product code:** C11CG68401PX

Product name : WF-C8690D3TWFC

- Benefit from A3 printing: Print in-house leaflets, brochure drafts, spreadsheets and more
- Ecological: Keep energy bills low and reduce your impact on the environment
- Save money: Further lower costs by changing consumables less
- Save time: Automatic double-sided printing, scanning, copying and faxing
- Built for business: DuraBrite Pro pigment inks

A3+, PrecisionCore, Print/Scan/Copy/Fax, 24 pages/min, 4800x1200 DPI, 33.6kbps, USB 3.0 B, LAN, Wi-Fi, USB 2.0, NFC, 772x873x1162 mm

Epson WorkForce Pro WF-C8690D3TWFC. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 4800 x 1200 DPI, Print speed (colour, normal quality, A4/US Letter): 35 ppm. Copying: Colour copying, Maximum copy resolution: 600 x 1200 DPI. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI. Faxing: Colour faxing. Duplex functions: Copy, Fax, Print, Scan. Maximum ISO A-series paper size: A3+. Wi-Fi. Direct printing. Product colour: White

Printing		Paper handling	
Duplex printing mode	Auto	Envelopes sizes	10, C4, C5, C6
Print technology *	Inkjet	Photo paper sizes	10x15, 13x18, 20x25
Printing *	Colour printing	Borderless printing media sizes	10x15, 13x18, 20x25
Duplex printing *	✓	Custom media width	55 - 127 mm
Maximum resolution *	4800 x 1200 DPI	Custom media length	330 - 1200 mm
Print speed (black, normal quality, A4/US Letter) *	35 ppm	Paper tray media weight	64 - 300 g/m ²
Print speed (colour, normal quality, A4/US Letter)	35 ppm	Multi-Purpose Tray media weight	64 - 300 g/m ²
Print speed (black, normal quality, A3)	13 ppm	Ports & interfaces	
Print speed (colour, normal quality, A3)	13 ppm	Direct printing *	✓
Print speed (ISO/IEC 24734) black	24 ppm	USB port	✓
Print speed (ISO/IEC 24734) colour	24 ppm	USB connector	USB Type-A / USB Type-B
Duplex print speed (black, normal quality, A4/US Letter)	16 ppm	USB 2.0 ports quantity	2
Duplex print speed (colour, normal quality, A4/US Letter)	16 ppm	USB 3.2 Gen 1 (3.1 Gen 1) ports quantity	1
Time to first page (black, normal)	5.5 s	Network	
Time to first page (colour, normal)	5.5 s	Wi-Fi *	✓
Copying		Ethernet LAN *	✓
Duplex copying *	✓	Cabling technology	10/100/1000Base-T(X)
Copying *	Colour copying	Ethernet LAN data rates	10, 100, 1000 Mbit/s
Maximum copy resolution *	600 x 1200 DPI	Wi-Fi standards	802.11a, 802.11b, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)
Maximum number of copies	999 copies	Near Field Communication (NFC)	✓
Copier resize	25 - 400%	Security algorithms	64-bit WEP, 128-bit WEP, WPA2-AES, WPA2-Enterprise
Scanning		Supported network protocols (IPv4)	TCP/IP
Duplex scanning *	✓	Supported network protocols (IPv6)	TCP/IP
Scanning *	Colour scanning	Management protocols	SNMP, HTTP, DHCP, BOOTP, APIPA, DDNS, mDNS, SNTP, SLP, WSD, LLTD, Ping
Optical scanning resolution *	1200 x 2400 DPI	Mobile printing technologies	Apple AirPrint, Epson Connect, Google Cloud Print
Scan technology	CIS	Performance	
Scan to	E-mail, FTP, Network folder, Software, USB	Card reader integrated	✗
Image formats supported	JPEG, TIFF	Sound pressure level (printing)	51 dB
Document formats supported	PDF	Sound power level (printing)	6.8 dB

Fax		Design	
Duplex faxing	✓	Product colour *	White
Faxing *	Colour faxing	Market positioning *	Business
Fax transmission speed	3 sec/page	Built-in display *	✓
Modem speed	33.6 Kbit/s	Display	LCD
Fax memory	550 pages	Display diagonal	12.7 cm (5")
Auto-redialing	✓	Control type	Touch
Speed dialling	✓	Colour display	✓
Fax forwarding	✓	Power	
Fax delayed sending	✓	Power consumption (copying)	39 W
Error Correction Mode (ECM)	✓	Power consumption (ready)	18 W
Features		Power consumption (sleep)	1.3 W
Recommended duty cycle	500 - 5000 pages per month	Power consumption (off)	0.2 W
Maximum duty cycle *	75000 pages per month	Energy Star Typical Electricity Consumption (TEC)	0.2 kWh/week
Duplex functions *	Copy, Fax, Print, Scan	AC input voltage	220 - 240 V
Printing colours *	Black, Cyan, Magenta, Yellow	System requirements	
Page description languages	ESC/P-R, PCL 5c, PCL 6, PDF 1.7, PostScript 3	Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64
Input & output capacity		Mac operating systems supported	Mac OS X 10.6 Snow Leopard
Total number of input trays *	3	Linux operating systems supported	✓
Total input capacity *	1835 sheets	Server operating systems supported	Windows Server 2003, Windows Server 2003 R2, Windows Server 2003 x64, Windows Server 2008, Windows Server 2008 R2, Windows Server 2008 x64, Windows Server 2012 R2, Windows Server 2012 x64, Windows Server 2016
Total output capacity *	250 sheets	Mobile operating systems supported	Android 4.0
Multi-Purpose tray	✓	Weight & dimensions	
Multi-Purpose tray input capacity	85 sheets	Width	772 mm
Auto document feeder (ADF)	✓	Depth	873 mm
Auto document feeder (ADF) input capacity	50 sheets	Height	1162 mm
Maximum input capacity	1835 sheets	Weight	104.8 kg
Paper handling		Packaging data	
Maximum ISO A-series paper size *	A3+	Package width	700 mm
Paper tray media types *	Thick paper	Package depth	800 mm
ISO A-series sizes (A0...A9) *	A3, A3+, A4, A5, A6	Package height	2200 mm
ISO B-series sizes (B0...B9)	B4, B5, B6	Package weight	138.5 kg
ISO C-series sizes (C0...C9)	C4, C6	Logistics data	
Non-ISO print media sizes	Executive, Legal, Letter, Tabloid (media size)	Harmonized System (HS) code	84433100



8715946673103

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.