



APC Parallel Maintenance Bypass Panel, 10-200kVA 400V wallmount, for Easy UPS 3S/3M

Brand : APC

Product code: E3MBPAR60K200H

Product name : Parallel Maintenance Bypass Panel, 10-200kVA 400V wallmount, for Easy UPS 3S/3M

- Features Schneider Electric breakers
- Compatible with Galaxy VL, Easy UPS 3-Phase Modular, and Easy UPS 3M Advanced UPSs
- Wall-mounted
- 1 year warranty
- Includes 3 Schneider Electric circuit breakers

Parallel Maintenance Bypass Panel, 10-200kVA 400V wallmount, for Easy UPS 3S/3M

[APC Parallel Maintenance Bypass Panel, 10-200kVA 400V wallmount, for Easy UPS 3S/3M:](#)

Maintenance bypass panel E3MBPAR60K200H for complete isolation of an Easy UPS 3M in parallel during service operations. Up to three UPSs can be isolated.

APC Parallel Maintenance Bypass Panel, 10-200kVA 400V wallmount, for Easy UPS 3S/3M. Product colour: White. Compliance certificates: RoHS. Width: 700 mm, Depth: 320 mm, Height: 1000 mm. Quantity per pack: 1 pc(s). Package width: 800 mm, Package depth: 570 mm, Package height: 1200 mm



Features		Weight & dimensions	
Product colour	White	Width	700 mm
Certificates		Depth	320 mm
Compliance certificates	RoHS	Height	1000 mm
Operational conditions		Weight	62 kg
Operating temperature (T-T)	0 - 40 °C	Packaging content	
Storage temperature (T-T)	-25 - 55 °C	Quantity per pack	1 pc(s)
Operating relative humidity (H-H)	0 - 95%	Manual	✓
Storage relative humidity (H-H)	0 - 95%	Packaging data	
		Package width	800 mm
		Package depth	570 mm
		Package height	1200 mm
		Package weight	92 kg



0731304346814



731304346814

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.