

ASUS ProArt PA27UCX-K computer monitor 68.6 cm (27") 3840 x 2160 pixels 4K Ultra HD LED Black

Brand : ASUS

Product family: ProArt

Product code: 90LM04NC-B02370

Product name : PA27UCX-K

27", IPS, 3840x2160, Off-Axis Contrast Optimization, HDR-10, Dolby Vision, HLG, 576 zones, $\Delta E < 1$, 97% DCI-P3, 99.5% Adobe RGB, 100% sRGB/Rec. 709, Hardware Calibration, USB-C, Calman Ready, ColourSpace Integration

ASUS ProArt PA27UCX-K. Display diagonal: 68.6 cm (27"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	Headphone out *	✓
Display resolution *	3840 x 2160 pixels	Headphone outputs	1
HD type *	4K Ultra HD	Headphone connectivity	3.5 mm
Native aspect ratio *	16:9	Ergonomics	
Display technology *	LED	VESA mounting *	✓
Panel type *	IPS	Panel mounting interface	100 x 100 mm
Touchscreen *	✗	Cable lock slot *	✓
Display brightness (typical)	1000 cd/m ²	Cable lock slot type	Kensington
Response time *	5 ms	Height adjustment *	✓
Display surface	Matt	Adjustable height (max)	12 cm
Screen shape *	Flat	Pivot	✓
Supported graphics resolutions	3840 x 2160	Pivot angle	-90 - 90°
Contrast ratio (typical) *	1000:1	Swivelling	✓
Contrast ratio (dynamic)	1000000:1	Swivel angle range	-60 - 60°
Maximum refresh rate *	144 Hz	Tilt adjustment	✓
Viewing angle, horizontal	178°	Tilt angle range	-5 - 23°
Viewing angle, vertical	178°	Picture-in-Picture	✓
Display number of colours *	1.073 billion colours	Power	
Pixel pitch	0.155 x 0.155 mm	Energy efficiency class (SDR) *	G
Viewable size, horizontal	59.6 cm	Energy efficiency class (HDR) *	G
Viewable size, vertical	33.5 cm	Energy consumption (SDR) per 1000 hours *	36 kWh
Digital horizontal frequency	40 - 144 kHz	Energy consumption (HDR) per 1000 hours *	43 kWh
Digital vertical frequency	30 - 60 Hz	Power consumption (typical) *	35.9 W
High Dynamic Range (HDR) supported	✓	Power consumption (standby) *	0.5 W
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)	Power consumption (off)	0.3 W
DDC/CI	✓	AC input voltage	100 - 240 V
sRGB coverage (typical)	100%	Energy efficiency scale	A to G
Adobe RGB coverage	99.5%	Weight & dimensions	
Performance		Width (with stand)	625.2 mm
Flicker-free technology	✓		

Performance		Weight & dimensions	
Low Blue Light technology	✓	Depth (with stand)	228.8 mm
Multimedia		Height (with stand)	544.5 mm
Number of speakers	2	Weight (with stand)	11.5 kg
RMS rated power	2 W	Width (without stand)	625.2 mm
Built-in speaker(s) *	✓	Depth (without stand)	91.3 mm
Built-in camera *	✗	Height (without stand)	367.1 mm
		Weight (without stand)	7.6 kg
Design		Packaging data	
Market positioning *	Graphics design	Package width	768 mm
Product colour *	Black	Package depth	479 mm
Feet colour	Black	Package height	355 mm
Ports & interfaces		Package weight	15.5 kg
Built-in USB hub *	✓	Package type	Box
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Packaging content	
USB upstream port type	USB Type-C	Stand included	✓
Number of upstream ports	1	Cables included	AC
USB Type-A downstream ports quantity	4	Other features	
DVI port	✗	Certification	BSMI, CB, CCC, CEL level , CU, ErP, FCC, ISO-9241-307, J-MOSS, KCC, Mac CompliantPSE, UkrSEPRO, UL/cUL, VCCI, WEEE, WHQL (Windows 10, Windows 8.1, Windows 7), MEPS, RCM, TUV Flicker-free , KC , eStandby, TUV Low Blue Light, ICES-3, PC recycle, VESA DisplayHDR 1000, CEC
HDMI *	✓		
HDMI ports quantity	2		
HDMI version	2.0b		
DisplayPorts quantity	1		
DisplayPort version	1.2		
Audio input	✗	Logistics data	
		Harmonized System (HS) code	85285210



4718017463317

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.