Brother LC462XLC ink cartridge 1 pc(s) Original High (XL) Yield Cyan



Brand : Brother

Product code: LC462XLC

Product name : LC462XLC

High Cyan Ink Yield Approx. 1,500 pages

Brother LC462XLC ink cartridge 1 pc(s) Original High (XL) Yield Cyan:

Colour Inkjet Multi-Function Centres

Brother Colour Inkjet MFCs are the perfect technology for your home and office. The range allows you to colour scan, copy, print and fax from one compact unit designed for your use. Eliminating the frustration of having to throw away unused inks, Brother's colour inkjet machines have separate ink cartridges for each colour. All you have to do is replace the empty cartridge - reducing waste and cost.

*Declared yield value in accordance with ISO/IEC 24711

Suitable for HK printer model only, consumable model number vaires from different country or area.

Benefits of Using Genuine Brother Ink Cartridges?
Specially Formulated Ink for Smooth Printing
Brother ink is specially formulated to achieve the right fluidity to flow through critical points of the print head with ease. This ensures a balanced distribution of ink on the page, resulting in a more optimal balance of colours.

Features	
Compatibility *	MFCJ3940DW, MFCJ3540DW, MFCJ2340DW, MFCJ2740DW
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1

Features	
Colour ink page yield *	1500 pages
Type *	Original
Cartridge capacity	High (XL) Yield
Printing colours *	Cyan
Brand compatibility *	Brother
Supply type *	Single pack

4977766816243

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date