

Epson PowerLite L210W 4500 ANSI lumens 3LCD WXGA (1280x800) White

Brand : Epson

Product family: PowerLite

Product code: V11HA70080

Product name : L210W



- 4,500 lumens brightness display Crisp images and bright colours, even in well-lit rooms
 - Laser projector Virtually maintenance-free performance for up to 30,000 hours (Eco)
 - Stream and share Wireless, MTR auto power-on by HDMI and easy smart stick connection
 - Fit and forget reliability Flexible, compact laser projector, comes with five-year warranty
 - The complete solution With an incredible contrast ratio of 2,500,000:1, the EB-L210W delivers vivid, lifelike content and defined shadow detail with deeper blacks
- 4500 Lm, 1024000 px (1280 x 800) x 3, 16:10, 2500000:1, 16W x 1, 30" - 300", 4.2kg

Epson PowerLite L210W 4500 ANSI lumens 3LCD WXGA (1280x800) White:

An affordable easy to use laser display solution with wireless connectivity and built-in speakers

Bring sharp images and bright colours to any meeting room with our super-bright new business projector combined with HD-ready WXGA resolution. The EB-L210W is designed to stream and share with wireless LAN, Screen Mirroring and split screen with two or four inputs in one display.

Projector		Ports & interfaces	
Smart projector *	✗	DVI port *	✗
Screen size compatibility *	762 - 7620 mm (30 - 300")	Network	
Projector brightness *	4500 ANSI lumens	Smart TV *	✗
Projection technology *	3LCD	Ethernet LAN *	✓
Projector native resolution *	WXGA (1280x800)	Wi-Fi *	✗
Contrast ratio (typical) *	2500000:1	Storage	
Native aspect ratio *	16:10	Card reader integrated *	✗
Keystone correction, horizontal	-30 - 30°	Features	
Keystone correction, vertical	-30 - 30°	Interactive *	✗
Matrix size	1.5 cm (0.59")	Noise level (economic mode)	27 dB
Light source		Noise level *	37 dB
Light source type *	Laser	Multimedia	
Service life of light source *	20000 h	Built-in speaker(s) *	✓
Service life of light source (economic mode)	30000 h	RMS rated power	16 W
Lens system		Number of built-in speakers	1
Focus *	Manual	Design	
Focal length range	18.2 - 29.1 mm	Market positioning *	Business
Aperture range (F-F)	1.51 - 1.77	Product colour *	White
Zoom capability	✓	Display	
Zoom type	Manual	Built-in display *	✗
Zoom ratio	1.16:1	Power	
Throw ratio	1.41 - 2.26	Power source *	AC
Video		Power consumption (typical) *	201 W
Analog signal format system *	Not supported	Power consumption (max)	260 W
Full HD *	✓	Power consumption (economy mode)	199 W
3D *	✗	AC input voltage	100 - 240 V
Ports & interfaces		AC input frequency	50/60 Hz
USB 2.0 ports quantity	2	Operational conditions	
USB 2.0 Type-A ports quantity	1	Operating temperature (T-T)	0 - 40 °C
USB 2.0 Type-B ports quantity	1		
Serial interface type *	RS-232C		
VGA (D-Sub) ports quantity *	2		

Ports & interfaces		Weight & dimensions	
HDMI ports quantity *	2	Width	325 mm
		Depth	299 mm
		Height	90 mm
		Weight *	4.2 kg
		Packaging content	
		Remote control included *	✓
		Batteries included	✓
		Cables included	AC, HDMI



8715946715476

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.