Lenovo 4XC7A80567 network card Internal Ethernet 25000 Mbit/s



Brand : Lenovo

Product code: 4XC7A80567

Product name : 4XC7A80567

ThinkSystem Broadcom 57504 10/25GbE SFP28 4-Port OCP Ethernet Adapter

Lenovo 4XC7A80567 network card Internal Ethernet 25000 Mbit/s:

The ThinkSystem Broadcom 57504 10/25GbE SFP28 4-port adapters are high-performance low-power 25 Gb Ethernet adapters with a PCIe 4.0 host interface that offers TruFlow intelligent flow processing and supports advanced networking technologies such as VXLAN, NVGRE, Geneve, RoCE, SDN and NFV, to facilitate the management of data networks and to enable service provider solutions.
Lenovo 4XC7A80567. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 25000 Mbit/s

Ports & interfaces	
Connectivity technology *	Wired
Host interface *	PCI Express
Interface *	Ethernet
PCI version	4.0

Network	
Maximum data transfer rate *	25000 Mbit/s
Networking standards *	IEEE 1588
Ethernet interface type	10 Gigabit Ethernet, 25 Gigabit Ethernet

Design	
Component for *	Server
Internal *	✔
Form factor	OCP 3.0

Design	
Certification	EN 55022:2010 + AC:2011 Class B (CE EU) EN 55024 Class B (EU) CFR47, Part 15 Class B (USA FCC) ICES-003 Class B (Canada) CNS13438 Class B (BSMI Taiwan) RRL KN22 Class B (S. Korea) KN24 (ESD) (S. Korea) V-3 / 2014 / 04 (VCCI Japan) EN 60950-1 UL 60950-1 CTUVus UL CSA 22.2 No. 950 CNS14336 Class B ICES 003 UL 1977 (connector safety) UL 796 (PCB wiring safety) UL 94 (flammability of parts)

Operational conditions	
Operating temperature (T-T)	0 - 55 °C
Storage temperature (T-T)	-40 - 70 °C
Operating relative humidity (H-H)	5 - 90%

Weight & dimensions	
Width	76 mm
Depth	115 mm

0889488603602

889488603602

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date