

ASUS PRIME B650M-K AMD B650 Socket AM5 micro ATX

Brand : ASUS

Product code: 90MB1F60-M0EAY0

Product name : PRIME B650M-K



- AMD AM5 Socket: Ready for AMD Ryzen™ 7000 Series Desktop Processors
- Ultrafast Connectivity: M.2 PCIe 5.0, Realtek 2.5Gb Ethernet, USB 3.2 Gen 2 ports, front USB 3.2 Gen 1 Type-C®

- ASUS OptiMem II: Careful routing of traces and vias, plus ground layer optimizations to preserve signal integrity for improved memory overclocking

- Comprehensive Cooling: VRM heatsink, M.2 heatsink, PCH heatsink, hybrid fan headers and Fan Xpert 2+

- Aura Sync RGB Lighting: Onboard Addressable Gen 2 headers and Aura RGB header for RGB LED strips, easily synced with Aura Sync-capable hardware

AMD B650 Micro-ATX motherboard with DDR5, PCIe 5.0 M.2, 2.5Gb Ethernet, HDMI, VGA, rear USB 3.2 Gen 2, front USB 3.2 Gen 1 Type-C, BIOS FlashBack, Aura Sync



Processor		Internal I/O	
Processor manufacturer *	AMD	12V power connector	✓
Processor socket *	Socket AM5	RGB LED pin header	✓
Compatible processor series *	AMD Ryzen 7000 Series	Rear panel I/O ports	
Supported processor sockets	Socket AM5	USB 2.0 ports quantity *	4
Memory		USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	2
Supported memory types *	DDR5-SDRAM	USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity *	2
Number of memory slots *	2	Ethernet LAN (RJ-45) ports *	1
Memory slots type	DIMM	PS/2 ports quantity	1
Memory channels	Dual-channel	VGA (D-Sub) ports quantity *	1
ECC compatibility	ECC & Non-ECC	HDMI ports quantity *	1
Supported memory clock speeds	4800,5000,5200,5400,5600,5800,6000,6200,6400 MHz	Headphone outputs	1
Supported memory clock speed (max)	6400 MHz	Line-in	✓
Maximum internal memory *	96 GB	Microphone in	✓
Unbuffered memory	✓	Network	
Storage controllers		Ethernet LAN	✓
Supported storage drive types	HDD & SSD	Ethernet interface type	2.5 Gigabit Ethernet
Supported storage drive interfaces *	M.2, SATA III	Wi-Fi *	✗
Number of HDDs supported	4	Features	
Number of storage drives supported	6	Motherboard chipset *	AMD B650
RAID support	✓	Audio output channels *	7.1 channels
RAID levels	0, 1, 10	Component for *	PC
Graphics		Motherboard form factor *	micro ATX
Parallel processing technology support *	Not supported	Motherboard chipset family *	AMD
Internal I/O		Windows operating systems supported	Windows 10 x64, Windows 11
USB 2.0 connectors *	2	Expansion slots	
USB 3.2 Gen 1 (3.1 Gen 1) connectors *	2	PCI Express x1 (Gen 4.x) slots	2
Number of SATA III connectors *	4	PCI Express x16 (Gen 4.x) slots	2
S/PDIF out connector	✓		
Audio connector	✓		

Internal I/O		Expansion slots	
Front panel audio connector	✓	Number of M.2 (M) slots	2
ATX Power connector (24-pin)	✓	BIOS	
CPU fan connector	✓	BIOS type *	UEFI AMI
Number of chassis fan connectors	2	BIOS memory size	256 Mbit
EPS power connector (8-pin)	✓	Packaging data	
Number of COM connectors	1	Package width	260 mm
TPM connector	✓	Package depth	270 mm
		Package height	51.5 mm
		Package weight	1.07 kg
		Weight & dimensions	
		Width	244 mm
		Depth	221 mm
		Packaging content	
		Cables included	SATA



4711387236628

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.