



HP E32k G5 4K USB-C PVC Free Monitor

Brand : HP

Product code: 6N4D6A5

Product name : E32k G5 4K USB-C PVC Free Monitor

E32k G5 4K USB-C PVC Free Monitor

[HP E32k G5 4K USB-C PVC Free Monitor:](#)

A Vision of Precision

Uniquely designed to deliver incredible visuals and extended flexibility, the HP E32k G5 4K USB-C Monitor redefines precision, so there's nothing between you and your best. Stylishly crafted with your comfort and the planet in mind, this 4K display is a powerhouse of productivity.

HP E32k G5 4K USB-C PVC Free Monitor. Display diagonal: 80 cm (31.5"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LCD, Display surface: Matt, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Network	
Display diagonal *	80 cm (31.5")	Ethernet LAN	✓
Display resolution *	3840 x 2160 pixels	Remotely operated	✓
HD type *	4K Ultra HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LCD	Panel mounting interface	100 x 100 mm
Panel type *	IPS	Cable lock slot *	✓
LED backlight	✓	Height adjustment *	✓
Backlight type	Edge LED	Adjustable height (max)	15 cm
Touchscreen *	✗	Pivot	✓
Display brightness (peak)	350 cd/m ²	Pivot angle	-90 - 90°
Display brightness (typical)	350 cd/m ²	Swivelling	✓
Display brightness	350 cd/m ²	Swivel angle range	-45 - 45°
Response time *	5 ms	Tilt adjustment	✓
Response time measurement type	GTG (Gray to Gray)	Tilt angle range	-5 - 20°
Display surface	Matt	On Screen Display (OSD)	✓
Anti-glare screen	✓	Power	
Screen shape *	Flat	Energy efficiency class (SDR) *	F
Supported graphics resolutions	1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1440 x 900 (WXGA+), 1600 x 1200 (UXGA), 1600 x 900, 1680 x 1050 (WSXGA+), 1920 x 1080 (HD 1080), 2560 x 1440, 3840 x 2160, 640 x 480 (VGA), 720 x 400, 720 x 480, 800 x 600 (SVGA)	Energy efficiency class (HDR) *	F
		Energy consumption (SDR) per 1000 hours *	32 kWh
		Power consumption (typical) *	39 W
		Power consumption (standby) *	0.5 W
		Power consumption (max)	210 W
Aspect ratio	16:9	Power consumption (off)	0.3 W
Contrast ratio (typical) *	1000:1	AC input voltage	100 - 240 V
Contrast ratio (dynamic)	8000000:1	AC input frequency	50/60 Hz
Maximum refresh rate *	60 Hz	Power supply type	Internal
Viewing angle, horizontal	178°	Energy efficiency scale	A to G
Viewing angle, vertical	178°	Operational conditions	
Display number of colours *	1.07 billion colours		
Response time (fast)	5 ms		

Display		Operational conditions	
Pixel pitch	0.18 x 0.18 mm	Operating temperature (T-T)	5 - 35 °C
Pixel density	140 ppi	Operating relative humidity (H-H)	20 - 80%
Horizontal scan range	30 - 135 kHz	Storage relative humidity (H-H)	20 - 80%
Vertical scan range	30 - 60 Hz	Weight & dimensions	
Viewable size, horizontal	69.7 cm	Width (with stand)	714 mm
Viewable size, vertical	39.2 cm	Depth (with stand)	227 mm
Digital horizontal frequency	30 - 135 kHz	Height (with stand)	603.4 mm
Digital vertical frequency	30 - 60 Hz	Weight (with stand)	8.4 kg
Display diagonal (metric)	80 cm	Width (without stand)	714 mm
Surface hardness	3H	Depth (without stand)	47 mm
Colour depth	10 bit	Height (without stand)	421.2 mm
Colour gamut	99%	Packaging data	
sRGB coverage (typical)	99%	Package width	820 mm
Performance		Package depth	527 mm
NVIDIA G-SYNC *	✗	Package height	161 mm
AMD FreeSync *	✗	Package weight	11.8 kg
Fast charging	✓	Package type	Box
Flicker-free technology	✓	Warranty card	✓
Low Blue Light technology	✓	Packaging content	
HP segment	Business	Stand included	✓
Multimedia		Cables included	AC
Number of speakers	2	Quick start guide	✓
RMS rated power	6 W	Bundled software	HP Display Center; HP Client Management Script Library
Built-in speaker(s) *	✓	Sustainability	
Built-in camera *	✗	Sustainability compliance	✓
Design		Sustainability certificates	ENERGY STAR, EPEAT, TCO, TCO10
Market positioning *	Business	Sustainable technologies and materials	Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Contains ocean-bound recycled plastic; 75% ITE-derived closed loop plastic; At least 25% recycled metal
Product colour *	Black		
Detachable stand	✓		
Feet colour	Silver, Black	Other features	
Ports & interfaces		Country of origin	China
Built-in USB hub *	✓	Introduction year	2023
USB hub version	3.2 Gen 1 (3.1 Gen 1)	UNSPSC-code	43211902
USB Type-A downstream ports quantity	3	Weight	8.4 kg
USB Type-C downstream ports quantity	1	Compliance certificates	CECP, CCC, CB, EAC, BIS, Federal Communications Commission (FCC), CE, BSMI
USB Type-C DisplayPort Alternate Mode	✓	Manufacturer warranty	3 years limited warranty
USB Power Delivery (USB PD)	✓	Ethernet LAN (RJ-45) ports	1
USB Power Delivery up to	65 W	Certification	BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; FCC; ISO 9241-307; KC/KCC; Korea MEPS (E-standby); NOM; PSB; SEPA; TUV-S; UL/CSA; VCCI; WEEE; ISC; ICE; UAE; TGM; Ukraine certificates; NRCS; PSE; Ukraine EE; CEL Grade 2
HDMI *	✓		
HDMI ports quantity	1		
HDMI version	2.0	Technical details	
DisplayPorts quantity	1	General Product Safety Regulation (GPSR) URL	https://support.hp.com/us-en/document/ish_6126692-6126777-16?openCLC=true
DisplayPort version	1.4		
HDCP	✓		



0196786615610



196786615610



0196786615757



196786615757




0196786615566



196786615566



0196786615702



196786615702



0196786615726



196786615726



0196786615672



196786615672



0196786615658



196786615658



5715063326947

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.