

Philips 4000 series TAG4106BK/00 headphones/headset Wired Head-band Gaming Black

Brand : Philips Product family: 4000 series Product code: TAG4106BK/00

Product name :
TAG4106BK/00

4000 Series TAG4106BK Gaming Headset

Philips 4000 series TAG4106BK/00 headphones/headset Wired Head-band Gaming Black:

Stylish design, leatherette earpads with memory foam, 50 mm precise acoustic drivers, detachable unidirectional microphone, and DTS surround sound provide great comfort and immersion during gameplay

Philips 4000 series TAG4106BK/00. Product type: Headset. Connectivity technology: Wired. Recommended usage: Gaming. Headphone frequency: 20 - 20000 Hz. Cable length: 1.8 m, Product colour: Black



Performance		Headphones	
Product type *	Headset	Driver type	Dynamic
Wearing style *	Head-band	Microphone	
Recommended usage *	Gaming	Microphone type *	Boom
Headset type *	Binaural	Microphone direction type	Unidirectional
Product colour *	Black	Detachable microphone	✓
Operating keys	Mute, Volume +, Volume -	Number of microphones	1
Volume control	Button	Weight & dimensions	
Control unit type	External control unit	Width	190 mm
Control type	Buttons	Depth	82 mm
Cable length	1.8 m	Height	222 mm
Cable colour	Black	Packaging data	
Adjustable headband	✓	Package width	225 mm
Plug and Play	✓	Package depth	108 mm
Ports & interfaces		Package height	245 mm
Connectivity technology *	Wired	Package type	Box
3.5 mm connector	✓	Packaging content	
USB connectivity	✓	Cables included	Audio (3.5mm)
Frequency response (music mode)	20 - 20000 Hz	Logistics data	
Headphones		Quantity per pack	1 pc(s)
Maximum input power	20 mW	Products per master (outer) case	3 pc(s)
Ear coupling *	Circumaural	Master (outer) case GTIN (EAN/UPC)	14895229126999
Acoustic system	Closed	Products per shipping (inner) case	1 pc(s)
Headphone frequency	20 - 20000 Hz	Shipping (inner) case GTIN (EAN/UPC)	24895229126996
Impedance	32 Ω	Other features	
Headphone sensitivity	101 dB	EAN/UPC/GTIN (packaging)	4895229126992
Magnet type	Neodymium		
Driver unit	5 cm		



4895229126992

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.