PHILIPS

Philips 7000 series SPK7207BL/00 mouse Office Ambidextrous USB Type-A Optical 1200 DPI



Brand : Philips **Product family:** 7000 series **Product code:** SPK7207BL/00

Product name : SPK7207BL/00

2000 series SPK7207BL Wired mouse

Philips 7000 series SPK7207BL/00 mouse Office Ambidextrous USB Type-A Optical 1200 DPI:

This mouse ensures a productive workspace. With its high-definition optical tracking and buttons that last millions of clicks, it's built to ensure reliability in any line of work.
Philips 7000 series SPK7207BL/00. Form factor: Ambidextrous. Movement detection technology: Optical, Device interface: USB Type-A, Movement resolution: 1200 DPI, Buttons type: Pressed buttons, Buttons quantity: 3, Scroll type: Wheel. Power source: Cable. Product colour: Black

Mouse	
Number of scroll wheels	1
Purpose *	Office
Connectivity technology *	Wired
Device interface *	USB Type-A
Movement detection technology *	Optical
Movement resolution *	1200 DPI
Buttons type	Pressed buttons
Scroll type *	Wheel
Buttons quantity *	3
Buttons durability (million clicks)	3

Design	
Form factor *	Ambidextrous
Ergonomic design	✔
Product colour *	Black
Surface coloration	Monochromatic

Ergonomics	
Cable length	1.5 m
Plug and Play	✔

Power	
Power source *	Cable

System requirements	
Windows operating systems supported	✔
Mac operating systems supported	✔
Linux operating systems supported	✔

Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	10 - 85 °C

Weight & dimensions	
Width	65 mm
Depth	110 mm
Height	35 mm
Weight	78 g

Packaging data	
Quantity per pack *	1 pc(s)

Technical details	
Driver requirement	✘

8712581797713

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date