

Targus EcoSmart AKB868UK keyboard Universal Bluetooth QWERTY UK English Black

Brand : Targus

Product family: EcoSmart

Product code: AKB868UK

Product name : AKB868UK



- CES Innovation-Award 2023 Honoree
- Manufactured From up to 85% Post-Consumer Recycled Plastic Materials, Finished in Sustainable Packaging
- Made with DefenseGuard™ Antimicrobial Protection* Which Creates a Cleaner Surface and Works Continuously to Help Prevent the Growth of Micro-Organisms
- Efficient Energy Harvesting Technology and Ultra-Low Power Bluetooth® BLE 5.0 Provides Practically Limitless Battery life in Ambient or Artificial light Conditions
- Large 1600 mAh Li-Polymer Battery, Rechargeable Via Photovoltaic Cells or USB-C® (Cable Included)
- Comfortable Typing Response Thanks to Tailor Made Targus® Keyset
- Enterprise Ready With Durable Scissored Key Design (Rated Up To 5 Million Key-Strokes)
- Backlit Keys With 3 Levels Of Adjustable Brightness (Up To 8 Hours Operation on Max. Setting)
- Familiar Comfort With Full-Sized, Triple Zoned Design With Dedicated Number Keypad
- Multi-Device Connectivity For Up to 3 Devices

Wireless, Bluetooth 5.0, 43.3 x 2 x 15.3 cm (W x H x D), Black, 0.84 kg



Keyboard		Power	
Recommended usage *	Universal	Power source type *	Battery
Connectivity technology *	Wireless	Keyboard battery type	Built-in battery
Device interface *	Bluetooth	Battery technology	Lithium Polymer (LiPo)
Keyboard layout *	QWERTY	Battery capacity	1600 mAh
Keyboard language *	UK English	Rechargeable	✓
Pointing device *	✗	Charging source	USB Type-C
Keyboard form factor *	Full-size (100%)	Mouse	
Numeric keypad *	✓	Mouse included *	✗
Multi-device support	✓	System requirements	
Bluetooth version	5.2	Windows operating systems supported	✓
Bluetooth Low Energy (BLE)	✓	Mac operating systems supported	✓
On/off switch	✓	Linux operating systems supported	✓
Design		Mobile operating systems supported	✓
Backlight *	✓	Weight & dimensions	
Backlight type	LED	Keyboard dimensions (WxDxH)	433 x 153 x 20 mm
Adjustable backlight	✓	Keyboard weight	840 g
Keyboard style	Straight		
Adjustable keyboard height	✓		
Product colour *	Black		



5051794042788

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.