

Samsung LC34G55TWWPXXU computer monitor 86.4 cm (34") 3440 x 1440 pixels UltraWide Quad HD LED Black

Brand : Samsung

Product family: Odyssey

Product code:
LC34G55TWWPXXU

Product name :
LC34G55TWWPXXU



- Screen: 3440x1440 Resolution, Curved 1000R, HDR10, VA Panel
 - Technology: 1ms MPRT Response Time, 165Hz Refresh Rate, FreeSync™
 - Connections: HDMI, Display Port, Headphone
 - Great For: Serious Gaming, Immersive Viewing and Productivity
 34" G55T UWQHD 165Hz Odyssey Gaming Monitor
 Samsung LC34G55TWWPXXU. Display diagonal: 86.4 cm (34"), Display resolution: 3440 x 1440 pixels, HD type: UltraWide Quad HD, Display technology: LED, Response time: 1 ms, Native aspect ratio: 21:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. VESA mounting. Product colour: Black

Display		Ergonomics	
Display diagonal *	86.4 cm (34")	Tilt adjustment	✓
Display resolution *	3440 x 1440 pixels	Tilt angle range	-2 - 18°
HD type *	UltraWide Quad HD	Black eQualizer function	✓
Native aspect ratio *	21:9		
Display technology *	LED		
Panel type *	VA		
Touchscreen *	✗		
Display brightness (typical)	250 cd/m²		
Display brightness (min)	200 cd/m²		
Response time *	1 ms		
Response time (MPRT)	1 ms		
Screen shape *	Curved		
Screen curvature rating	1000R		
Contrast ratio (typical) *	2500:1		
Dynamic contrast ratio marketing name	Mega Infinity DCR		
Maximum refresh rate *	165 Hz		
Refresh rate optimizor	✓		
Viewing angle, horizontal	178°		
Viewing angle, vertical	178°		
Display number of colours *	16.7 million colours		
Viewable size, horizontal	79.7 cm		
Viewable size, vertical	33.4 cm		
High Dynamic Range (HDR) supported	✓		
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)		
Colour gamut standard	NTSC		
Colour gamut	72%		
NTSC coverage (typical)	72%		
Performance		Power	
AMD FreeSync *	✓	Energy efficiency class (SDR) *	G
AMD FreeSync type	FreeSync Premium	Energy efficiency class (HDR) *	G
Flicker-free technology	✓	Energy consumption (SDR) per 1000 hours *	32 kWh
Game features	Super Arena Gaming UX, Screen Size Optimizer	Energy consumption (HDR) per 1000 hours *	50 kWh
		Power consumption (typical) *	32.4 W
		Power consumption (standby) *	0.5 W
		Power consumption (max)	55 W
		Power consumption (off)	0.3 W
		AC input voltage	100 - 240 V
		Power supply type	External
		Energy efficiency scale	A to G
		Annual energy consumption	47 kWh
		Operational conditions	
		Operating temperature (T-T)	10 - 40 °C
		Operating relative humidity (H-H)	10 - 80%
		Non-operating relative humidity (non-condensing)	10 - 80%
		Weight & dimensions	
		Width (with stand)	806.6 mm
		Depth (with stand)	272.6 mm
		Height (with stand)	475.3 mm
		Weight (with stand)	5.6 kg
		Width (without stand)	806.6 mm
		Depth (without stand)	152.7 mm
		Height (without stand)	380.9 mm
		Weight (without stand)	5.2 kg
		Packaging data	
		Package width	901 mm

Performance		Packaging data	
Smart modes	AOS, Dynamic, Cinema, Custom, FPS, RPG, RTS	Package depth	441 mm
Multimedia		Package height	216 mm
Built-in speaker(s) *	✗	Package weight	7.9 kg
Design		Packaging content	
Market positioning *	Gaming	Cables included	DisplayPort
Product colour *	Black	Installation CD	✓
Ports & interfaces		Power cable length	1.5 m
HDMI *	✓	Other features	
HDMI ports quantity	1	Brand specific technologies	Eye Saver, Black Equalizer
HDMI version	2.0	Low input lag	✓
DisplayPorts quantity	1	Picture-by-Picture (PbP)	✓
DisplayPort version	1.4	USB sound bar (Ready)	✗
Headphone out *	✓	Disclaimer	✓
Ergonomics		Off Timer Plus	✓
VESA mounting *	✓	Certification	Windows 10
Panel mounting interface	75 x 75 mm	Logistics data	
Wall mountable	✓	Harmonized System (HS) code	85285210
Height adjustment *	✗		



8806094862195

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.