

StarTech.com Dual TV Ceiling Mount - Back-to-Back Heavy Duty Hanging Dual Screen Mount with Adjustable Telescopic Pole - Tilt/Swivel/Rotate - VESA Bracket for 32"-75" Displays

Brand : StarTech.com

Product code: FPCEILBTB

Product name : Dual TV Ceiling Mount - Back-to-Back Heavy Duty Hanging Dual Screen Mount with Adjustable Telescopic Pole - Tilt/Swivel/Rotate - VESA Bracket for 32"-75" Displays



StarTech.com Dual TV Ceiling Mount, Hanging 2 Screen VESA Pole Mount for 32"-75" Displays - Height Adjustable Telescopic Pole

StarTech.com Dual TV Ceiling Mount - Back-to-Back Heavy Duty Hanging Dual Screen Mount with Adjustable Telescopic Pole - Tilt/Swivel/Rotate - VESA Bracket for 32"-75" Displays. Maximum weight capacity: 90 kg, Minimum screen size: 81.3 cm (32"), Maximum screen size: 190.5 cm (75"), Minimum VESA mount: 200 x 200 mm, Maximum VESA mount: 600 x 400 mm. Height adjustment range: 1060 - 1560 mm, Tilt angle range: -20 - 5°. Product colour: Black

Mounting		Weight & dimensions	
Maximum weight capacity *	90 kg	Weight	9.8 kg
Minimum screen size	81.3 cm (32")	Packaging data	
Number of displays supported *	2	Package width	310 mm
Maximum weight capacity (per display) *	45 kg	Package depth	935 mm
Maximum screen size *	190.5 cm (75")	Package height	145 mm
Mounting type *	Ceiling	Package weight	10.8 kg
Minimum VESA mount *	200 x 200 mm	Packaging content	
Maximum VESA mount *	600 x 400 mm	Manual	✓
Panel mounting interface	200 x 200, 300 x 300, 400 x 200, 400 x 400, 600 x 400	Screws included	✓
Ergonomics		Number of screws	46
Height adjustment	✓	Wrench included	✓
Height adjustment range	1060 - 1560 mm	Nuts included	✓
Tilt angle range	-20 - 5°	Number of nuts	2
Swivel angle range	-180 - 180°	Washers included	✓
Angle of rotation	360°	Number of washers included	12
Adjustable	✓	Spacer included	✓
Design		Number of spacers included	32
Product colour *	Black	Technical details	
Housing material	Steel	Sustainability compliance	✓
Anti-theft function	✗	Compliance certificates	CE, RoHS
Weight & dimensions		Logistics data	
Width	165 mm	Harmonized System (HS) code	85299097
Depth	680 mm	Master (outer) case width	340 mm
Depth (max)	68 cm	Master (outer) case length	965 mm
Height	835 mm	Master (outer) case height	310 mm
		Products per master (outer) case	2 pc(s)



065030880671

Catalog Object Cloud