



BenQ MW855UST+ Ultra short throw projector 3500 ANSI lumens DLP WXGA (1280x800) 3D Black, White

Brand : BenQ

Product code: 9H.JKS77.24E

Product name : MW855UST+

- Classroom Interaction
- Ultra short-throw ratio
- DLP technology for long-lasting picture perfection
- PointWrite Interactive Solution Compatible

DLP, 1280x800, 3500 lm, 16:10, RMS 2x 10W, HDMI, VGA, RS-232, USB, IR, 287.5x206.9x373.3 mm
BenQ MW855UST+. Projector brightness: 3500 ANSI lumens, Projection technology: DLP, Projector native resolution: WXGA (1280x800). Light source type: Lamp, Service life of light source: 5000 h, Service life of light source (economic mode): 8000 h. Focus: Manual, Fixed focal length: 2.5 mm, Aperture range (F-F): 2.5 - 2.5. Analog signal format system: NTSC, PAL, SECAM, Supported graphics resolutions: 640 x 480 (VGA), 720 x 400, 800 x 600 (SVGA), 832 x 624, 1024 x 768 (XGA), 1152 x 864 (XGA+), 1152..., Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232, HDMI connector type: Full-size



Projector		Network	
Screen size compatibility *	2032 - 2540 mm (80 - 100")	Smart TV *	✗
Projector brightness *	3500 ANSI lumens	Ethernet LAN *	✓
Projection technology *	DLP	Ethernet LAN (RJ-45) ports	1
Projector native resolution *	WXGA (1280x800)	Wi-Fi *	✗
Contrast ratio (typical) *	10000:1	Storage	
Native aspect ratio *	16:10	Card reader integrated *	✗
Number of colours	1.073 billion colours	Features	
Horizontal scan range	15 - 102 kHz	Noise level (economic mode)	29 dB
Vertical scan range	23 - 120 Hz	On Screen Display (OSD)	✓
Keystone correction, horizontal	-15 - 15°	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, Dutch, English, Spanish, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Romanian, Russian, Swedish, Thai, Turkish
Keystone correction, vertical	-15 - 15°		
Matrix size	1.65 cm (0.65")	Number of OSD languages	28
Matrix type	DMD	Noise level *	34 dB
Light source		Multimedia	
Light source type *	Lamp	Built-in speaker(s) *	✓
Service life of light source *	5000 h	RMS rated power	20 W
Service life of light source (economic mode)	8000 h	Number of built-in speakers	2
Lamp power	240 W	Design	
Lamps quantity	1 lamp(s)	Product type *	Ultra short throw projector
Lens system		Product colour *	Black, White
Focus *	Manual	Placement	Desktop
Fixed focal length	2.5 mm		
Aperture range (F-F)	2.5 - 2.5		
Zoom type	Fixed		
Throw ratio	0.35		
Vertical lens shift range	-2 - 2%		
Offset	122%		

Video		Design	
Analog signal format system *	NTSC, PAL, SECAM	Cable lock slot	✓
3D *	✓	Cable lock slot type	Kensington
Supported graphics resolutions	640 x 480 (VGA), 720 x 400, 800 x 600 (SVGA), 832 x 624, 1024 x 768 (XGA), 1152 x 864 (XGA+), 1152 x 870, 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768 (WXGA), 1280 x 800 (WXGA), 1280 x 960, 1360 x 768 (WXGA), 1400 x 1050 (SXGA+), 1440 x 900 (WXGA+), 1600 x 1200 (UXGA), 1680 x 1050 (WSXGA+), 1920 x 1080 (HD 1080), 1920 x 1200 (WUXGA)	Display	
		Built-in display *	✗
		Power	
		Power source *	AC
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p	Power consumption (typical) *	320 W
		Power consumption (standby) *	0.5 W
		Power consumption (max)	350 W
		Power consumption (economy mode)	260 W
Ports & interfaces		AC input voltage	100 - 240 V
HDMI connector type	Full-size	AC input frequency	50 - 60 Hz
USB 2.0 ports quantity	1	Operational conditions	
USB 2.0 Type-B ports quantity	1	Operating temperature (T-T)	0 - 40 °C
Mini-USB 2.0 ports quantity	1	Storage temperature (T-T)	-20 - 60 °C
Audio (L/R) in *	1	Operating relative humidity (H-H)	10 - 90%
Serial interface type *	RS-232	Storage relative humidity (H-H)	10 - 90%
PC Audio in	✓	Weight & dimensions	
PC Audio out	✓	Width	287.5 mm
VGA (D-Sub) ports quantity *	2	Depth	373.3 mm
HDMI ports quantity *	2	Height	206.9 mm
Composite video in *	1	Weight *	5 kg
DVI port *	✗	Packaging content	
AC (power) in	✓	Remote control included *	✓
		Batteries included	✓
		Cables included	AC, VGA
		Manual	✓
		Logistics data	
		Harmonized System (HS) code	85286200



4718755077456

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.