

StarTech.com 2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch - USB Powered

Brand : StarTech.com

Product code: SV211HDUA

Product name : 2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch - USB Powered

StarTech.com 2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch - USB Powered KVM with HDMI - Dual Port HDMI KVM Switch
StarTech.com 2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch - USB Powered.
Keyboard port type: USB, Mouse port type: USB, Video port type: HDMI. Maximum resolution: 1920 x 1200 pixels, Maximum digital resolution: 1920 x 1200 pixels. Product colour: Black, Housing material: Plastic, Cable length: 0.85 m. Windows operating systems supported: Windows 10, Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10..., Mac operating systems supported: Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks, Server operating systems supported: Windows Server 2003, Windows Server 2008 R2, Windows Server 2012, Windows Server 2016, Windows.... Compliance certificates: RoHS



Ports & interfaces

Number of computers controlled *	2
Keyboard port type *	USB
Mouse port type *	USB
Video port type *	HDMI
Console ports *	3.5mm headphone, 3.5mm mic, HDMI, USB A
Console USB ports quantity	2
Audio connections	✓

Network

Ethernet LAN	✗
--------------	---

Performance

Maximum resolution *	1920 x 1200 pixels
Maximum digital resolution	1920 x 1200 pixels
HDCP	✓
Hot-Plug support	✓
Daisy chain	✗

Design

Rack mounting *	✗
Product colour *	Black
Housing material	Plastic
Cable length	0.85 m
LED indicators	✓
Certification	FCC, CE, REACH

Display

Built-in display *	✗
--------------------	---

Power		System requirements	
USB powered	✓		Windows 10, Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 Pro, Windows 10 Pro x64, Windows 2000, Windows 2000 Professional, Windows 7, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 7 x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8 x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows Vista x64, Windows XP, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64
		Windows operating systems supported	Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
		Mac operating systems supported	Windows Server 2003, Windows Server 2008 R2, Windows Server 2012, Windows Server 2016, Windows Server 2019
		Server operating systems supported	
Sustainability			
Compliance certificates		RoHS	
Operational conditions			
Operating temperature (T-T)		0 - 40 °C	
Storage temperature (T-T)		-20 - 60 °C	
Operating relative humidity (H-H)		0 - 90%	
Weight & dimensions			
Width		66 mm	
Depth		88 mm	
Height		23 mm	
Weight		350 g	
Packaging data			
Package width		161 mm	
Package depth		250 mm	
Package height		62 mm	
Package weight		464 g	
Packaging content			
Manual		✓	
Software included		✓	

Other features	
Audio support	✓
IP control	✗
Logistics data	
Harmonized System (HS) code	85176200



0065030851060



065030851060



0841601326218



841601326218



5054533527652

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.