

Epson Squirrel Multipack 6-colours 378 Claria Photo HD Ink

Brand : Epson Product family: Squirrel Product code: C13T37884010

Product name : Multipack 6-colours 378 Claria Photo HD Ink

Multipack 6-colours 378 Claria Photo HD Ink
Epson Squirrel Multipack 6-colours 378 Claria Photo HD Ink. Cartridge capacity: Standard Yield, Black ink volume: 5.5 ml, Supply type: Multi pack, Colour ink volume: 4.1 ml, Printing colours: Black, Cyan, Light Cyan, Magenta, Light magenta, Yellow, Quantity per pack: 1 pc(s)



Features		Logistics data	
Print technology	Inkjet printing	Pallet gross width	120 cm
Compatibility *	- Expression Photo XP-8500 - Expression Photo HD XP-15000	Pallet gross height	100 cm
Quantity per pack *	1 pc(s)	Products per pallet	540 pc(s)
Black ink cartridges quantity	1	Pallet gross weight	0 g
Colour ink cartridges quantity	5	Master (outer) case width	195 mm
Black ink volume	5.5 ml	Master (outer) case length	370 mm
Colour ink volume	4.1 ml	Master (outer) case height	150 mm
Type *	Original	Products per master (outer) case	5 pc(s)
Cartridge capacity	Standard Yield	Master (outer) case gross weight	0 g
Ink type	Pigment-based ink	Master (outer) case GTIN (EAN/UPC)	8715946648989
Printing colours *	Black, Cyan, Light Cyan, Magenta, Light magenta, Yellow	Harmonized System (HS) code	84439990
Brand compatibility *	Epson	Pallet width (UK)	100 cm
Supply type *	Multi pack	Pallet length (UK)	120 cm
OEM code	C13T37884010	Pallet height (UK)	2 m
Country of origin	Indonesia	Pallet weight (UK)	0 g
Packaging data		Products per pallet (UK)	540 pc(s)
Package width	144 mm	Products per pallet layer	60 pc(s)
Package depth	192 mm	Products per pallet layer (UK)	60 pc(s)
Package height	70 mm	Minimum order quantity	5 pc(s)
Package weight	208 g		
Package type	Blister		



8715946646473



4058154242971

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.