



BenQ RP8603 Interactive flat panel 2.18 m (86") LCD Wi-Fi 450 cd/m² 4K Ultra HD Black Touchscreen Built-in processor Android 11 18/7

Brand : BenQ

Product code: 9H.F84TK.DE1

Product name : RP8603

- Germ-resistant screen, pen, and remote
 - Built-in air ionizer for clean air
 - 2 x 16W speakers with subwoofer for immersive sound
 - One-tap NFC login to instantly load lesson materials
 - Interactive teaching tools for more hands-on lessons
- 86", 4K UHD (3840 x 2160), 9H, 1200:1, 450 nits, IR Touch, A73x2 + A53x2, Mali- G52 MP8, Android 11.0

BenQ RP8603. Product design: Interactive flat panel. Display diagonal: 2.18 m (86"), Display technology: LCD, Display resolution: 3840 x 2160 pixels, Display brightness: 450 cd/m², HD type: 4K Ultra HD, Touchscreen. Wi-Fi. Operating hours (hours/days): 18/7. Operating system installed: Android 11. Product colour: Black



Display		Design	
Panel type	IPS	Anti-glare screen	✓
Display diagonal *	2.18 m (86")	Performance	
Display technology *	LCD	Purpose *	Education
Display resolution *	3840 x 2160 pixels	Operating hours (hours/days)	18/7
Display brightness *	450 cd/m ²	Power	
HD type *	4K Ultra HD	Power consumption (typical) *	141.9 W
Touchscreen *	✓	Power consumption (standby) *	0.5 W
Touchscreen technology	Infrared	AC input voltage	100 - 240 V
Number of simultaneous touchpoints	40	AC input frequency	50 - 60 Hz
Native aspect ratio	16:9	Computer system	
Response time	8 ms	Computer system *	✓
Contrast ratio (typical)	1200:1	Built-in processor *	✓
Contrast ratio (dynamic)	30000:1	Processor architecture	ARM Cortex A73 + ARM Cortex A53
Panel life	50000 h	Internal memory	8 GB
RGB colour space	NTSC	Internal storage capacity	64 GB
Ports & interfaces		Operating system installed	Android 11
HDMI ports quantity *	4	Weight & dimensions	
HDMI version	2.0	Display width	1962.4 mm
HDMI input ports quantity	3	Display depth	121.5 mm
HDMI output ports quantity	1	Display height	1203.4 mm
DVI port *	✗	Display weight	70.2 kg
VGA (D-Sub) input ports	1	Packaging data	
DisplayPorts quantity *	1	Package width	2160 mm
USB port *	✓	Package depth	250 mm
USB version	2.0/3.2 Gen 1 (3.1 Gen 1)	Package height	1340 mm
USB connector type	USB Type-A, USB Type-B, USB Type-C	Package weight	87 kg
Ethernet LAN (RJ-45) ports	2		

Ports & interfaces		Packaging content	
PC Audio in	✓	Remote control included	✓
Microphone in	✓	Stylus pen	✓
OPS module slot	✓	Cables included	AC, HDMI, USB, USB Type-C, VGA
Audio		Mounting kit	✓
		Operational conditions	
Built-in speaker(s) *	✓	Operating temperature (T-T)	0 - 40 °C
Number of built-in speakers	2	Operating relative humidity (H-H)	20 - 80%
RMS rated power	32 W	Storage temperature (T-T)	-10 - 60 °C
Design		Storage relative humidity (H-H)	10 - 60%
Product design *	Interactive flat panel		
Placement supported *	Indoor		
Product colour *	Black		
VESA mounting *	✓	Network	
Panel mounting interface	800 x 600 mm	Ethernet LAN *	✓
		Ethernet LAN data rates	10,100,1000 Mbit/s
		Wi-Fi *	✓



0840046046903



840046046903



4718755088469

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.