

Epson V12HB09080 document camera White 25.4 / 3.2 mm (1 / 3.2") CMOS USB/HDMI/Wi-Fi



Brand : Epson

Product code: V12HB09080

Product name : V12HB09080

- High-definition classroom content 4K UHD wireless visualiser with 13 mega-pixel camera and 60fps
- Fully flexible and portable Dual band wireless connectivity and lightweight design
- See every detail in large format 230x zoom ratio and microscope attachment
- Capture and record Capture real time content in 4K and share with others
- Complete peace of mind 5-year warranty as standard

1/ 3.2 " CMOS, 4K UHD, 4208 x 3120 px, 13 Mp, 362 x 159 x 85 mm / 586 x 159 x 554 mm, 2.8 kg
 Epson V12HB09080. Effective sensor resolution: 13 MP, Optical sensor size: 25.4 / 3.2 mm (1 / 3.2"),
 Sensor type: CMOS. Optical zoom: 10x, Digital zoom: 23x, Shooting area (WxD): 297 x 420 mm.
 Interface: USB/HDMI/Wi-Fi, USB connector type: Mini-USB B, USB Type-A, Wi-Fi standards: 802.11a,
 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac). Power consumption (typical): 9.6 W, Power
 consumption (standby): 0.5 W. Width: 586 mm, Depth: 159 mm, Height: 554 mm

Camera		Technical details	
Effective sensor resolution *	13 MP	Product colour *	White
Optical sensor size *	25.4 / 3.2 mm (1 / 3.2")	Control type	Buttons
Sensor type *	CMOS	Display modes	Microscope, Motion
Supported graphics resolutions *	320 x 180, 320 x 240, 320 x 288 (QVGA), 640 x 360, 640 x 480 (VGA), 1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768 (WXGA), 1600 x 1200 (UXGA), 1920 x 1080 (HD 1080), 2560 x 1920	Anti-flicker	✓
		LED indicators	✓
		Cable lock slot	✓
		Cable lock slot type	Kensington
HD type	4K Ultra HD	Frame rate	60 fps
Maximum frame rate	60 fps	Warranty period	5 year(s)
Lens system		Power	
Auto focus	✓	Power consumption (typical)	9.6 W
Optical zoom	10x	Power consumption (standby)	0.5 W
Digital zoom	23x	Weight & dimensions	
Shooting area (WxD)	297 x 420 mm	Width	586 mm
Ports & interfaces		Depth	159 mm
Interface *	USB/HDMI/Wi-Fi	Height	554 mm
HDMI input ports quantity	1	Weight	2.8 kg
HDMI output ports quantity	1	Dimensions folded (WxDxH)	362 x 159 x 85 mm
USB connector type	Mini-USB B, USB Type-A	Packaging data	
USB 1.1 ports quantity	1	Quantity per pack	1 pc(s)
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)		



8715946717708

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.